



Simply energy saving

MASTER TL-D Eco

The MASTER TL-D Eco lamp offers the same light output as a MASTER TL-D Super 80 lamp, while using less energy, thanks to the use of specific phosphors and a special gas filling. Application areas are schools, offices, governmental buildings and healthcare environments.

Benefits

- Simple lamp-for-lamp replacement for more than 10% energy savings
- Makes lighting installations compliant with latest indoor lighting standards
- Relatively high efficacy, both initially and during lifetime, with high lumen maintenance

Features

- The only T8 fluorescent lamp that saves more than 10% of energy in existing luminaires with electromagnetic gear
- Lower power savings with electronic gear depending on type of gear (current- or power-controlled)
- Can be directly retrofitted into existing fluorescent fittings operating on electromagnetic or electronic gear in indoor applications
- Uses the latest highly efficient phosphors and special filling gas
- High-quality lighting with good color rendering (CRI > 80)
- Light output comparable to other TL-D Super 80 colors
- Lumen maintenance and lifetime the same as other TL-D Super 80 colors
- Dimmable

MASTER TL-D Eco

Application

- For use in indoor applications with room temperatures above 20 °C (which implies temperature around the lamp of over 25-35 °C)
- Primary focus on offices, schools and hospitals; secondary focus on retail, industry, supermarkets
- Not recommended under the following conditions: - with air flow around the lamps - in luminaires with active air handling (lamp temperature will not be the required 25-35 °C, but room temperature) - in open luminaires/battens very close to air conditioning outlets or cold air flows - in space above freezers (temperature may easily drop below 20 °C) - in combination with VRUs (voltage reduction units)

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-D8ECO

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Eco 32W/840 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

