



CoreLine Waterproof – the clear choice for LED

CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 50% energy savings compared with TL-D
- Reliable LED technology – maintenance-free
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

Features

- Reliable integrated LED technology, ensuring maintenance-free installation and a long lifetime
- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets

Application




- Parking garages
- Warehouses
- General lighting

CoreLine Waterproof


Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.


Dimensional drawing




Product details




CoreLine Waterproof WT120C G2
PCU-7DPP



CoreLine Waterproof WT120C G2
PCU-3DPP




CoreLine Waterproof WT120C G2
PCU-10DPP




CoreLine Waterproof WT120C G2
PCU-9DPP

CoreLine Waterproof


Product details




CoreLine Waterproof WT120C G2
PCU-12DPP




CoreLine waterproof G2 (WT120C
G2),MDU, Motion Detection Unit




CoreLine Waterproof WT120C G2
PCU-2DPP




CoreLine Waterproof WT120C G2
PCU-13DPP




CoreLine Waterproof WT120C G2
PCU-8DPP



CoreLine waterproof G2 (WT120C
G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2
PCU-11DPP



CoreLine waterproof G2 (WT120C
G2),Emergency lighting, TrustSight

CoreLine Waterproof

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	1.6

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

Approval and Application

CE mark	Yes
Protection class IEC	Safety class I
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Mech. impact protection code	IK08
Ingress protection code	IP65

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Lamp		Product	
		family code	Embedded control	family code	Service tag
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	LED27S	-	WT130C	Yes
96248700	WT120C G2 LED27S/840 PSU MDU L1200	LED27S	Movement and light sensor (On/Off)	WT130C	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	LED27S	Movement and light sensor (On/Off)	WT130C	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	LED27S	-	WT130C	Yes
88307500	WT120C G2 LED27S/840 PSD L1200	LED27S	-	WT130C	Yes
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	LED27S	-	WT130C	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	LED40S	-	WT130C	Yes
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	LED40S	Movement and light sensor (On/Off)	WT130C	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	LED40S	-	WT130C	Yes
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	LED40S	-	WT130C	Yes
88309900	WT120C G2 LED40S/840 PSD L1200	LED40S	-	WT130C	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	LED40S	-	WT130C	Yes
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	LED40S	Movement and light sensor (On/Off)	WT130C	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	LED40S	-	WT130C	Yes
84046600	WT120C G2 LED27S/840 PSU L1200	-	-	-	Yes
84048000	WT120C G2 LED40S/840 PSU L1200	-	-	-	Yes
36933499	WT120C G2 LED40S/865 PSU L1200	-	-	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	-	-	Yes
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	-	-	Yes
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	-	-	Yes
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	-	-	Yes
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	-	-	Yes
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	-	-	Yes
96244900	WT120C G2 LED19S/840 PSU MDU L600	LED27S	Movement and light sensor (On/Off)	WT130C	Yes
88306800	WT120C G2 LED19S/840 PSD L600	LED19S	-	WT130C	Yes
84045900	WT120C G2 LED19S/840 PSU L600	-	-	-	Yes

Order Code	Full Product Name	Lamp		Product	
		family code	Embedded control	family code	Service tag
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	LED34S	-	WT130C	Yes
96267800	WT120C G2 LED34S/840 PSU MDU L1500	LED34S	Movement and light sensor (On/Off)	WT130C	Yes
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	LED34S	Movement and light sensor (On/Off)	WT130C	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	LED34S	-	WT130C	Yes
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	LED34S	-	WT130C	Yes
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	LED34S	Movement and light sensor (On/Off)	WT130C	Yes
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	LED34S	-	WT130C	Yes
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	LED60S	-	WT130C	Yes
96275300	WT120C G2 LED60S/840 PSU MDU L1500	LED60S	Movement and light sensor (On/Off)	WT130C	Yes
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	LED60S	Movement and light sensor (On/Off)	WT130C	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	LED60S	-	WT130C	Yes
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	LED60S	-	WT130C	Yes
88310500	WT120C G2 LED60S/840 PSD L1500	LED60S	-	WT130C	Yes
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	LED60S	-	WT130C	Yes
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	LED60S	Movement and light sensor (On/Off)	WT130C	Yes
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	LED60S	-	WT130C	Yes
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	LED80S	-	WT130C	Yes
96286900	WT120C G2 LED80S/840 PSU MDU L1500	LED80S	-	WT130C	Yes
40929600	WT120C G2 LED80S/840 PSD L1500	LED80S	-	WT130C	Yes
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	LED80S	-	WT130C	Yes
97578400	WT120C G2 LED65S/840 WIA L1500	-	-	WT130C	-
84047300	WT120C G2 LED34S/840 PSU L1500	-	-	-	Yes
84049700	WT120C G2 LED60S/840 PSU L1500	-	-	-	Yes
40928900	WT120C G2 LED80S/840 PSU L1500	-	-	-	Yes
36934199	WT120C G2 LED34S/865 PSU L1500	-	-	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-	-	-

Light Technical

CoreLine Waterproof

Order Code	Full Product Name	Optic type
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Wide beam
96248700	WT120C G2 LED27S/840 PSU MDU L1200	Wide beam
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	Wide beam
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Wide beam
88307500	WT120C G2 LED27S/840 PSD L1200	Wide beam
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Wide beam
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Wide beam
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Wide beam
16316700	WT120C G2 LED40S/840 PSU WEC L1200	Wide beam
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Wide beam
88309900	WT120C G2 LED40S/840 PSD L1200	Wide beam
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Wide beam
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Wide beam
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Wide beam
84046600	WT120C G2 LED27S/840 PSU L1200	Wide beam
84048000	WT120C G2 LED40S/840 PSU L1200	Wide beam
36933499	WT120C G2 LED40S/865 PSU L1200	Wide beam
34976399	WT120C G2 LED18S/840 PSU PCO L600	Very wide beam
34977099	WT120C G2 LED25S/840 PSU PCO L1200	Very wide beam
34978799	WT120C G2 LED31S/840 PSU PCO L1500	Very wide beam
34979499	WT120C G2 LED37S/840 PSU PCO L1200	Very wide beam
34980099	WT120C G2 LED57S/840 PSU PCO L1500	Very wide beam
34981799	WT120C G2 LED75S/840 PSU PCO L1500	Very wide beam
96244900	WT120C G2 LED19S/840 PSU MDU L600	Wide beam
88306800	WT120C G2 LED19S/840 PSD L600	Wide beam
84045900	WT120C G2 LED19S/840 PSU L600	Wide beam

Order Code	Full Product Name	Optic type
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Wide beam
96267800	WT120C G2 LED34S/840 PSU MDU L1500	Wide beam
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	Wide beam
88308200	WT120C G2 LED34S/840 PSD L1500	Wide beam
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Wide beam
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Wide beam
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Wide beam
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Wide beam
96275300	WT120C G2 LED60S/840 PSU MDU L1500	Wide beam
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Wide beam
16318100	WT120C G2 LED60S/840 PSU WEC L1500	Wide beam
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Wide beam
88310500	WT120C G2 LED60S/840 PSD L1500	Wide beam
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Wide beam
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Wide beam
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Wide beam
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Wide beam
96286900	WT120C G2 LED80S/840 PSU MDU L1500	Wide beam
40929600	WT120C G2 LED80S/840 PSD L1500	Wide beam
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Wide beam
97578400	WT120C G2 LED65S/840 WIA L1500	Wide beam
84047300	WT120C G2 LED34S/840 PSU L1500	Wide beam
84049700	WT120C G2 LED60S/840 PSU L1500	Wide beam
40928900	WT120C G2 LED80S/840 PSU L1500	Wide beam
36934199	WT120C G2 LED34S/865 PSU L1500	Wide beam
36935899	WT120C G2 LED60S/865 PSU L1500	Wide beam

Temperature

Order Code	Full Product Name	Ambient temperature range
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-20 to +35 °C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C
88307500	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-20 to +35 °C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	0 to +25 °C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C
84048000	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C
36933499	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C
34976399	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C
96244900	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C
88306800	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-20 to +35 °C
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	0 to +25 °C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-20 to +35 °C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	0 to +25 °C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
40929600	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C
97578400	WT120C G2 LED65S/840 WIA L1500	-20 to +35 °C
84047300	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No
96248700	WT120C G2 LED27S/840 PSU MDU L1200	No
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	No
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	No
88307500	WT120C G2 LED27S/840 PSD L1200	Yes
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	No
16316700	WT120C G2 LED40S/840 PSU WEC L1200	No
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No
88309900	WT120C G2 LED40S/840 PSD L1200	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes
84046600	WT120C G2 LED27S/840 PSU L1200	No
84048000	WT120C G2 LED40S/840 PSU L1200	No
36933499	WT120C G2 LED40S/865 PSU L1200	No
34976399	WT120C G2 LED18S/840 PSU PCO L600	No
34977099	WT120C G2 LED25S/840 PSU PCO L1200	No
34978799	WT120C G2 LED31S/840 PSU PCO L1500	No
34979499	WT120C G2 LED37S/840 PSU PCO L1200	No
34980099	WT120C G2 LED57S/840 PSU PCO L1500	No
34981799	WT120C G2 LED75S/840 PSU PCO L1500	No
96244900	WT120C G2 LED19S/840 PSU MDU L600	No
88306800	WT120C G2 LED19S/840 PSD L600	Yes
84045900	WT120C G2 LED19S/840 PSU L600	No

Order Code	Full Product Name	Dimmable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No
96267800	WT120C G2 LED34S/840 PSU MDU L1500	No
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	No
88308200	WT120C G2 LED34S/840 PSD L1500	Yes
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	No
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No
96275300	WT120C G2 LED60S/840 PSU MDU L1500	No
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	No
16318100	WT120C G2 LED60S/840 PSU WEC L1500	No
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
88310500	WT120C G2 LED60S/840 PSD L1500	Yes
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	No
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	No
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
96286900	WT120C G2 LED80S/840 PSU MDU L1500	No
40929600	WT120C G2 LED80S/840 PSD L1500	Yes
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No
97578400	WT120C G2 LED65S/840 WIA L1500	Wireless Dim
84047300	WT120C G2 LED34S/840 PSU L1500	No
84049700	WT120C G2 LED60S/840 PSU L1500	No
40928900	WT120C G2 LED80S/840 PSU L1500	No
36934199	WT120C G2 LED34S/865 PSU L1500	No
36935899	WT120C G2 LED60S/865 PSU L1500	No

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96248700	WT120C G2 LED27S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
88307500	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
16316700	WT120C G2 LED40S/840 PSU WEC L1200	(0.38,0.38)SDCM<=3
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3
88309900	WT120C G2 LED40S/840 PSD L1200	(0.38,0.38)SDCM<=3
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	(0.38,0.38)SDCM<=3
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)SDCM<=3
84048000	WT120C G2 LED40S/840 PSU L1200	(0.38,0.38)SDCM<=3

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity
36933499	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)SDCM<=3
34976399	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)SDCM<=3
34977099	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34978799	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
34979499	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34980099	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
34981799	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
96244900	WT120C G2 LED19S/840 PSU MDU L600	(0.38,0.38)SDCM<=3
88306800	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)SDCM<=3
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96267800	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
96275300	WT120C G2 LED60S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3
16318100	WT120C G2 LED60S/840 PSU WEC L1500	(0.38,0.38)SDCM<=3
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3
88310500	WT120C G2 LED60S/840 PSD L1500	(0.38,0.38)SDCM<=3
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96286900	WT120C G2 LED80S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
40929600	WT120C G2 LED80S/840 PSD L1500	(0.38,0.38)SDCM<=3
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	(0.38,0.38)SDCM<=3
97578400	WT120C G2 LED65S/840 WIA L1500	(0.38,0.38)SDCM<=3
84047300	WT120C G2 LED34S/840 PSU L1500	(0.38,0.38)SDCM<=3
84049700	WT120C G2 LED60S/840 PSU L1500	(0.38,0.38)SDCM<=3
40928900	WT120C G2 LED80S/840 PSU L1500	(0.38,0.38)SDCM<=3
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)SDCM<=3
36935899	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)SDCM<=3

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Not applicable	Not applicable
96248700	WT120C G2 LED27S/840 PSU MDU L1200	Not applicable	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	Not applicable	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Not applicable	Not applicable
88307500	WT120C G2 LED27S/840 PSD L1200	1%	Not applicable
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	1%	Not applicable
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Not applicable	Not applicable
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Not applicable	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	Not applicable	Not applicable
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Not applicable	Not applicable
88309900	WT120C G2 LED40S/840 PSD L1200	1%	Not applicable
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Not applicable	Not applicable
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Not applicable	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	1%	Not applicable
84046600	WT120C G2 LED27S/840 PSU L1200	Not applicable	Not applicable
84048000	WT120C G2 LED40S/840 PSU L1200	Not applicable	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
36933499	WT120C G2 LED40S/865 PSU L1200	Not applicable	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	Not applicable	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	Not applicable	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	Not applicable	Not applicable
34979499	WT120C G2 LED37S/840 PSU PCO L1200	Not applicable	Not applicable
34980099	WT120C G2 LED57S/840 PSU PCO L1500	Not applicable	Not applicable
34981799	WT120C G2 LED75S/840 PSU PCO L1500	Not applicable	Not applicable
96244900	WT120C G2 LED19S/840 PSU MDU L600	Not applicable	Yes
88306800	WT120C G2 LED19S/840 PSD L600	1%	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	Not applicable	Not applicable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Not applicable	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	Not applicable	Yes
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	Not applicable	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	1%	Not applicable
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Not applicable	Not applicable
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Not applicable	Yes

CoreLine Waterproof

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	1%	Not applicable
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Not applicable	Not applicable
96275300	WT120C G2 LED60S/840 PSU MDU L1500	Not applicable	Yes
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Not applicable	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	Not applicable	Not applicable
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Not applicable	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	1%	Not applicable
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Not applicable	Not applicable
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	1%	Not applicable
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Not applicable	Not applicable
96286900	WT120C G2 LED80S/840 PSU MDU L1500	Not applicable	Yes
40929600	WT120C G2 LED80S/840 PSD L1500	1%	Not applicable
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Not applicable	Not applicable
97578400	WT120C G2 LED65S/840 WIA L1500	10%	Not applicable
84047300	WT120C G2 LED34S/840 PSU L1500	Not applicable	Not applicable
84049700	WT120C G2 LED60S/840 PSU L1500	Not applicable	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	Not applicable	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	Not applicable	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	Not applicable	Not applicable

