



Philips TubePoint Gen 2: versatile, high performance and long-lasting tunnel lighting

TubePoint gen2

Many tunnel authorities have outdated tunnel lighting installations that urgently need replacing, but have only a limited budget to achieve it. Philips TubePoint Gen2 is the perfect solution. It's the cost-effective solution that's the result of years of experience in tunnel lighting and underpass lighting, combined with the latest technologies developed by Philips. With its modular design and state-of-the-art LED architecture, TubePoint Gen2 is a versatile, cost-effective luminaire that meets the most stringent tunnel lighting requirements. Manufactured from the highest-quality components that are specifically designed for tunnels, these tunnel luminaires promise a long lifetime, great performance and low maintenance costs. The lighting efficiency and wide choice of optics means the number of luminaires required for an installation can be reduced significantly compared with conventional solutions. And a high lumen per watt ratio at system level improves the total cost of ownership. TubePoint Gen2 is part of the Philips TotalTunnel solution for complete tunnel lighting. A solution you can trust for versatile, high performance lighting in traffic tunnels.

Benefits

- Versatile luminaire range suitable all types of traffic tunnels
- Economical LED solution for point source tunnel lighting schemes
- High performance and efficient
- Quick and easy mounting

TubePoint gen2


Features

- Wide range of optics and lumen packages
- Mounting and connectivity options
- Option of a remote driver
- Compatible with tunnel controls from Philips and third parties
- Service tag: QR-based identification for maintenance, installation and spare part information


Application

- Tunnel
- Underpass

Versions





TubePoint GEN2-BGP235



TubePoint GEN2-BGP236

Dimensional drawing



TubePoint gen2

Product details




TubePoint_GEN2-BGP235_MB-DPP.TIF

TubePoint_GEN2-BGP235-1DPP.TIF



TubePoint_GEN2-BGP235_MBQ-S-2DPP.TIF

TubePoint_GEN2-BGP236-1DPP.TIF



TubePoint_GEN2-BGP235_MBQ_M-DPP.TIF

TubePoint_GEN2-BGP235_BA_SO-8DPP.TIF



TubePoint_GEN2-BGP235_MBQ_S-DPP.TIF

TubePoint_GEN2-BGP235-2DPP.TIF



TubePoint gen2

Product details



TubePoint_GEN2-BGP235_BA-DPP.TIF



TubePoint_GEN2-BGP235_MBQ_L-DPP.TIF



TubePoint_GEN2-BGP235_MBA-DPP.TIF



TubePoint_GEN2-BGP236-2DPP.TIF

TubePoint gen2

General Information	
Driver included	Yes
Light source replaceable	Yes
Service tag	Yes
Light Technical	
Luminaire light beam spread	101° x 158°
Light source color	740 neutral white
Optical cover/lens type	Flat glass
Optic type outdoor	Distribution symmetrical medium 11
Standard tilt angle side entry	0°
Standard tilt angle posttop	-
Upward light output ratio	0
Controls and Dimming	
Dimmable	Yes
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Mech. impact protection code	IK09
Surge Protection (Common/ Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Application Conditions	
Maximum dim level	10%

General Information

Order Code	Full Product Name	Lamp family code	Number of gear units	Product family code
48290900	BGP235 LED30-4S/740 DSM11 D9 MIO-CIO MBQ	LED30	1 unit	BGP235
48291600	BGP235 LED50-4S/740 DSM11 D9 MIO-CIO MBQ	LED50	1 unit	BGP235
48292300	BGP235 LED90-4S/740 DSM11 D9 MIO-CIO MBQ	LED90	1 unit	BGP235
48293000	BGP235 LED120-4S/740 DSM11 D9 MIO-CIO MB	LED120	1 unit	BGP235
48294700	BGP235 LED180-4S/740 DSM11 D9 MIO-CIO MB	LED180	1 unit	BGP235
48296100	BGP236 LED360-4S/740 DSM11 D9 MIO-CIO MB	LED360	2 units	BGP236

Light Technical

Order Code	Full Product Name	Number of light sources
48290900	BGP235 LED30-4S/740 DSM11 D9 MIO-CIO MBQ	20
48291600	BGP235 LED50-4S/740 DSM11 D9 MIO-CIO MBQ	20
48292300	BGP235 LED90-4S/740 DSM11 D9 MIO-CIO MBQ	28

Order Code	Full Product Name	Number of light sources
48293000	BGP235 LED120-4S/740 DSM11 D9 MIO-CIO MB	40
48294700	BGP235 LED180-4S/740 DSM11 D9 MIO-CIO MB	56
48296100	BGP236 LED360-4S/740 DSM11 D9 MIO-CIO MB	112

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
48290900	BGP235 LED30-4S/740 DSM11 D9 MIO-CIO MBQ	0.53 %
48291600	BGP235 LED50-4S/740 DSM11 D9 MIO-CIO MBQ	0.5 %
48292300	BGP235 LED90-4S/740 DSM11 D9 MIO-CIO MBQ	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
48293000	BGP235 LED120-4S/740 DSM11 D9 MIO-CIO MB	0.5 %
48294700	BGP235 LED180-4S/740 DSM11 D9 MIO-CIO MB	0.5 %
48296100	BGP236 LED360-4S/740 DSM11 D9 MIO-CIO MB	0.5 %

TubePoint gen2

