



Adaptable high-bay lighting offering high efficiency and connectivity options to lighting systems and software applications.

GentleSpace Gen3

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

GentleSpace Gen3

Benefits

- High-quality visibility combined with great uniformity and reduced glare
- A robust and reliable solution for a long service life
- A highly efficient solution, offering an attractive total cost of ownership
- Flexibility enabled by a high degree of adaptability to changing application needs
- Ready to be connected to existing and upcoming system and software applications
- Extensive application coverage including food production, manufacturing different height ceilings, hallways

Features

- High efficiency (HE) of up to 174 lm/W
- Long service life of the L80 at 100 K hrs
- Extreme version (XT) up to 70 °C
- Detachable mounting system for ease of installation
- Fully compliant with EN-12464-1; low-glare rating and colour rendering of ≥ 80
- Option for dust cover to meet the requirements of the food industry
- Suitable for new builds or point-for-point replacement of HPI 250 W, HPL 400 W or HPI 400 W, reducing energy consumption by up to 65%
- A wide variety of optics (WB/MB/NB/XNB and HRO) to meet application requirements, also with the option of adjustable optics variants (NBA) with the flexibility to shift from NB to WB with an easy adjustment mechanism
- Safety Class I or II
- Interact Industry and Philips GreenWarehouse-ready
- Swimming pool protected version (SWP)

Application

- Food production and manufacturing
- Warehouses and logistics centres
- Indoor sports halls, swimming pools and exhibition halls

Versions



New Highbay



New Highbay



New Highbay



New Highbay

GentleSpace Gen3

Versions



GentleSpace Gen3



GentleSpace Gen3



New Highbay



New Highbay



GentleSpace Gen3 - -

Application Conditions

Maximum dimming level	10%
-----------------------	-----

Approval and Application

Ingress protection code	IP65
-------------------------	------

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	D
Glow-wire test	850/5
Light source replaceable	Yes
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Init. Colour rendering index	>80
Luminous flux tolerance	+/-10%

-

Order Code	Full Product Name	Driver failure rate at 5,000 hours
40730800	BY481P LED250S/840 PSD WB GC SI	0.5 %
40731500	BY481P LED250S/840 PSD MB GC SI	0.5 %
40732200	BY481P LED350S/840 PSD MB GC SI	0.5 %
40734600	BY481P LED250S/840 PSD NB GC SI	0.5 %
40741400	BY481P LED250S/840 PSD WB PC SI	0.5 %
40743800	BY481P LED350S/840 PSD WB GC SI	0.5 %
40744500	BY481P LED250S/840 PSD MB PC SI	0.5 %
40763600	BY481P LED250S/840 PSD HRO GC SI	0.5 %
40767400	BY481P LED350S/840 PSD HRO GC SI	0.5 %
40768100	BY481P LED350S/840 PSD NB GC SI	0.5 %
40769800	BY481P LED250S/840 PSD HRO PC SI	0.5 %
40793300	BY481P LED350S/840 PSD WB PC SI	0.5 %
40795700	BY481P LED250S/840 PSD NB PC SI	0.5 %
40798800	BY481P LED350S/840 PSD MB PC SI	0.5 %
40799500	BY481P LED350S/840 PSD HRO PC SI	0.5 %
40733900	BY480P LED130S/840 PSD WB GC SI	0.5 %
40736000	BY480P LED170S/840 PSD WB GC SI	0.5 %
40738400	BY480P LED130S/840 PSD MB GC SI	0.5 %
40739100	BY480P LED170S/840 PSD HRO GC SI	0.5 %
40742100	BY480P LED130S/840 PSD HRO GC SI	0.5 %
40745200	BY480P LED170S/840 PSD MB GC SI	0.5 %
40785800	BY480P LED130S/840 PSD NB GC SI	0.5 %
40828200	BY480P LED170S/865 PSD WB GC SI	-
01089500	BY480P LED130S/865 PSD WB GC SI	-
01090100	BY482P LED170S/840 PSD WB GC SI	-
01092500	BY480P LED130S/840 PSD WB GC SI XT	-
01093200	BY480P LED170S/840 PSD WB GC SI XT	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	0.5 %
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	0.5 %
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	0.5 %
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	0.5 %
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	0.5 %
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	0.5 %
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	0.5 %
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	0.5 %
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	-
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	-
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	-
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	0.5 %
40758200	BY481P LED250S/840 PSD WB GC SI BR	0.5 %
40778000	BY481P LED250S/840 PSD NB GC SI BR	0.5 %
40786500	BY481P LED250S/840 PSD HRO GC SI BR	0.5 %
40790200	BY481P LED350S/840 PSD MB GC SI BR	0.5 %
40801500	BY481P LED350S/840 PSD WB GC SI BR	0.5 %
40757500	BY481P LED250S/840 PSD MB GC WH	0.5 %
40771100	BY481P LED250S/840 PSD MB PC WH	0.5 %
40777300	BY481P LED250S/840 PSD WB GC WH	0.5 %
40800800	BY481P LED250S/840 PSD HRO GC WH	0.5 %
40830500	BY481P LED250S/865 PSD WB GC SI	-
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	-

Order Code	Full Product Name	Driver failure rate at 5,000 hours
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	-
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	-
01091800	BY483P LED250S/840 PSD WB GC SI	-
01094900	BY481P LED250S/840 PSD WB GC SI XT	-
01095600	BY481P LED350S/840 PSD WB GC SI XT	-
01102100	BY481P LED250S/840 PSED WB GC SI	-
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	-
40760500	BY480P LED130S/840 PSD WB GC WH	0.5 %
40776600	BY480P LED130S/840 PSD MB GC WH	0.5 %
40766700	BY480P LED130S/840 PSD WB GC SI BR	0.5 %
40781000	BY481P LED250S/840 PSD MB GC WH BR	0.5 %
40788900	BY481P LED250S/840 PSD WB GC WH BR	0.5 %
41152700	BY481P LED350S/865 PSD WB PC SI BR	-
41463400	BY480P LED130S/840 PSD NBA GC SI	0.5 %
41464100	BY480P LED170S/840 PSD NBA GC SI	0.5 %
41465800	BY481P LED250S/840 PSD NBA GC SI	0.5 %
41466500	BY481P LED350S/840 PSD NBA GC SI	0.5 %
41467200	BY481P LED350S/840 PSD NBA PC SI	0.5 %
41468900	BY481P LED250S/840 PSD NBA PC SI	0.5 %
41469600	BY480P LED130S/840 PSD NBA PC SI	0.5 %
41470200	BY480P LED170S/840 PSD NBA PC SI	0.5 %

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Suitable for random switching	Order Code	Full Product Name	Ambient temperature range	Suitable for random switching
40730800	BY481P LED250S/840 PSD WB GC SI	-30 to +45 °C	No	40795700	BY481P LED250S/840 PSD NB PC SI	-30 to +45 °C	No
40731500	BY481P LED250S/840 PSD MB GC SI	-30 to +45 °C	No	40798800	BY481P LED350S/840 PSD MB PC SI	-30 to +45 °C	No
40732200	BY481P LED350S/840 PSD MB GC SI	-30 to +45 °C	No	40799500	BY481P LED350S/840 PSD HRO PC SI	-30 to +45 °C	No
40734600	BY481P LED250S/840 PSD NB GC SI	-30 to +45 °C	No	40733900	BY480P LED130S/840 PSD WB GC SI	-30 to +45 °C	No
40741400	BY481P LED250S/840 PSD WB PC SI	-30 to +45 °C	No	40736000	BY480P LED170S/840 PSD WB GC SI	-30 to +45 °C	No
40743800	BY481P LED350S/840 PSD WB GC SI	-30 to +45 °C	No	40738400	BY480P LED130S/840 PSD MB GC SI	-30 to +45 °C	No
40744500	BY481P LED250S/840 PSD MB PC SI	-30 to +45 °C	No	40739100	BY480P LED170S/840 PSD HRO GC SI	-30 to +45 °C	No
40763600	BY481P LED250S/840 PSD HRO GC SI	-30 to +45 °C	No	40742100	BY480P LED130S/840 PSD HRO GC SI	-30 to +45 °C	No
40767400	BY481P LED350S/840 PSD HRO GC SI	-30 to +45 °C	No	40745200	BY480P LED170S/840 PSD MB GC SI	-30 to +45 °C	No
40768100	BY481P LED350S/840 PSD NB GC SI	-30 to +45 °C	No	40785800	BY480P LED130S/840 PSD NB GC SI	-30 to +45 °C	No
40769800	BY481P LED250S/840 PSD HRO PC SI	-30 to +45 °C	No	40828200	BY480P LED170S/865 PSD WB GC SI	-30 to +45 °C	No
40793300	BY481P LED350S/840 PSD WB PC SI	-30 to +45 °C	No	01089500	BY480P LED130S/865 PSD WB GC SI	-30 to +45 °C	No

GentleSpace Gen3

Order Code	Full Product Name	Ambient temperature range	Suitable for random switching
01090100	BY482P LED170S/840 PSD WB GC SI	-30 to +45 °C	No
01092500	BY480P LED130S/840 PSD WB GC SI XT	-40 to +70 °C	No
01093200	BY480P LED170S/840 PSD WB GC SI XT	-30 to +60 °C	No
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	-30 to +45 °C	Yes
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	-30 to +45 °C	Yes
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	-30 to +45 °C	Yes
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	-30 to +45 °C	Yes
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	-30 to +45 °C	Yes
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	-30 to +45 °C	Yes
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	-30 to +45 °C	Yes
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	-30 to +45 °C	Yes
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	-30 to +45 °C	Yes
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	-30 to +45 °C	Yes
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	-30 to +45 °C	Yes
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	-30 to +45 °C	Yes
40750600	BY481P LED250S/840 PSD MB GC SI BR	-30 to +45 °C	No
40758200	BY481P LED250S/840 PSD WB GC SI BR	-30 to +45 °C	No
40778000	BY481P LED250S/840 PSD NB GC SI BR	-30 to +45 °C	No
40786500	BY481P LED250S/840 PSD HRO GC SI BR	-30 to +45 °C	No
40790200	BY481P LED350S/840 PSD MB GC SI BR	-30 to +45 °C	No
40801500	BY481P LED350S/840 PSD WB GC SI BR	-30 to +45 °C	No
40757500	BY481P LED250S/840 PSD MB GC WH	-30 to +45 °C	No
40771100	BY481P LED250S/840 PSD MB PC WH	-30 to +45 °C	No
40777300	BY481P LED250S/840 PSD WB GC WH	-30 to +45 °C	No

Order Code	Full Product Name	Ambient temperature range	Suitable for random switching
40800800	BY481P LED250S/840 PSD HRO GC WH	-30 to +45 °C	No
40830500	BY481P LED250S/865 PSD WB GC SI	-30 to +45 °C	No
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	-30 to +45 °C	No
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	-30 to +45 °C	No
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	-30 to +45 °C	No
01091800	BY483P LED250S/840 PSD WB GC SI	-30 to +45 °C	No
01094900	BY481P LED250S/840 PSD WB GC SI XT	-40 to +70 °C	No
01095600	BY481P LED350S/840 PSD WB GC SI XT	-30 to +60 °C	No
01102100	BY481P LED250S/840 PSED WB GC SI	-30 to +45 °C	No
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	-30 to +45 °C	No
40760500	BY480P LED130S/840 PSD WB GC WH	-30 to +45 °C	No
40776600	BY480P LED130S/840 PSD MB GC WH	-30 to +45 °C	No
40766700	BY480P LED130S/840 PSD WB GC SI BR	-30 to +45 °C	No
40781000	BY481P LED250S/840 PSD MB GC WH BR	-30 to +45 °C	No
40788900	BY481P LED250S/840 PSD WB GC WH BR	-30 to +45 °C	No
41152700	BY481P LED350S/865 PSD WB PC SI BR	-30 to +45 °C	No
41463400	BY480P LED130S/840 PSD NBA GC SI	-30 to +45 °C	No
41464100	BY480P LED170S/840 PSD NBA GC SI	-30 to +45 °C	No
41465800	BY481P LED250S/840 PSD NBA GC SI	-30 to +45 °C	No
41466500	BY481P LED350S/840 PSD NBA GC SI	-30 to +45 °C	No
41467200	BY481P LED350S/840 PSD NBA PC SI	-30 to +45 °C	No
41468900	BY481P LED250S/840 PSD NBA PC SI	-30 to +45 °C	No
41469600	BY480P LED130S/840 PSD NBA PC SI	-30 to +45 °C	No
41470200	BY480P LED170S/840 PSD NBA PC SI	-30 to +45 °C	No

Approval and Application

GentleSpace Gen3

Order Code	Full Product Name	Mech. impact protection code
40730800	BY481P LED250S/840 PSD WB GC SI	IK07
40731500	BY481P LED250S/840 PSD MB GC SI	IK07
40732200	BY481P LED350S/840 PSD MB GC SI	IK07
40734600	BY481P LED250S/840 PSD NB GC SI	IK07
40741400	BY481P LED250S/840 PSD WB PC SI	IK08
40743800	BY481P LED350S/840 PSD WB GC SI	IK07
40744500	BY481P LED250S/840 PSD MB PC SI	IK08
40763600	BY481P LED250S/840 PSD HRO GC SI	IK07
40767400	BY481P LED350S/840 PSD HRO GC SI	IK07
40768100	BY481P LED350S/840 PSD NB GC SI	IK07
40769800	BY481P LED250S/840 PSD HRO PC SI	IK08
40793300	BY481P LED350S/840 PSD WB PC SI	IK08
40795700	BY481P LED250S/840 PSD NB PC SI	IK08
40798800	BY481P LED350S/840 PSD MB PC SI	IK08
40799500	BY481P LED350S/840 PSD HRO PC SI	IK08
40733900	BY480P LED130S/840 PSD WB GC SI	IK07
40736000	BY480P LED170S/840 PSD WB GC SI	IK07
40738400	BY480P LED130S/840 PSD MB GC SI	IK07
40739100	BY480P LED170S/840 PSD HRO GC SI	IK07
40742100	BY480P LED130S/840 PSD HRO GC SI	IK07
40745200	BY480P LED170S/840 PSD MB GC SI	IK07
40785800	BY480P LED130S/840 PSD NB GC SI	IK07
40828200	BY480P LED170S/865 PSD WB GC SI	IK07
01089500	BY480P LED130S/865 PSD WB GC SI	IK07
01090100	BY482P LED170S/840 PSD WB GC SI	IK07
01092500	BY480P LED130S/840 PSD WB GC SI XT	IK07
01093200	BY480P LED170S/840 PSD WB GC SI XT	IK07
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	IK02
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	IK02
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	IK02
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	IK02
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	IK02
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	IK02
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	IK02
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	IK02
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	IK02

Order Code	Full Product Name	Mech. impact protection code
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	IK02
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	IK02
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	IK02
40750600	BY481P LED250S/840 PSD MB GC SI BR	IK07
40758200	BY481P LED250S/840 PSD WB GC SI BR	IK07
40778000	BY481P LED250S/840 PSD NB GC SI BR	IK07
40786500	BY481P LED250S/840 PSD HRO GC SI BR	IK07
40790200	BY481P LED350S/840 PSD MB GC SI BR	IK07
40801500	BY481P LED350S/840 PSD WB GC SI BR	IK07
40757500	BY481P LED250S/840 PSD MB GC WH	IK07
40771100	BY481P LED250S/840 PSD MB PC WH	IK08
40777300	BY481P LED250S/840 PSD WB GC WH	IK07
40800800	BY481P LED250S/840 PSD HRO GC WH	IK07
40830500	BY481P LED250S/865 PSD WB GC SI	IK07
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	IK07
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	IK07
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	IK07
01091800	BY483P LED250S/840 PSD WB GC SI	IK07
01094900	BY481P LED250S/840 PSD WB GC SI XT	IK07
01095600	BY481P LED350S/840 PSD WB GC SI XT	IK07
01102100	BY481P LED250S/840 PSED WB GC SI	IK07
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	IK07
40760500	BY480P LED130S/840 PSD WB GC WH	IK07
40776600	BY480P LED130S/840 PSD MB GC WH	IK07
40766700	BY480P LED130S/840 PSD WB GC SI BR	IK07
40781000	BY481P LED250S/840 PSD MB GC WH BR	IK07
40788900	BY481P LED250S/840 PSD WB GC WH BR	IK07
41152700	BY481P LED350S/865 PSD WB PC SI BR	IK07
41463400	BY480P LED130S/840 PSD NBA GC SI	IK07
41464100	BY480P LED170S/840 PSD NBA GC SI	IK07
41465800	BY481P LED250S/840 PSD NBA GC SI	IK07
41466500	BY481P LED350S/840 PSD NBA GC SI	IK07
41467200	BY481P LED350S/840 PSD NBA PC SI	IK08
41468900	BY481P LED250S/840 PSD NBA PC SI	IK08
41469600	BY480P LED130S/840 PSD NBA PC SI	IK08
41470200	BY480P LED170S/840 PSD NBA PC SI	IK08

General Information (1/2)

Order Code	Full Product Name	Beam angle	Optical	Lamp
		of light source	Cap cover/ lens type	family code
40730800	BY481P LED250S/840 PSD WB GC SI	114 °	-	-
40731500	BY481P LED250S/840 PSD MB GC SI	114 °	-	-
40732200	BY481P LED350S/840 PSD MB GC SI	114 °	-	-
40734600	BY481P LED250S/840 PSD NB GC SI	114 °	-	-

Order Code	Full Product Name	Beam angle	Optical	Lamp
		of light source	Cap cover/ lens type	family code
40741400	BY481P LED250S/840 PSD WB PC SI	114 °	-	-
40743800	BY481P LED350S/840 PSD WB GC SI	114 °	-	-
40744500	BY481P LED250S/840 PSD MB PC SI	114 °	-	-
40763600	BY481P LED250S/840 PSD HRO GC SI	114 °	-	-

GentleSpace Gen3

Order Code	Full Product Name	Beam angle of light source	Cap base	Optical cover/ lens type	Lamp family code
40767400	BY481P LED350S/840 PSD HRO GC SI	114 °	-	-	-
40768100	BY481P LED350S/840 PSD NB GC SI	114 °	-	-	-
40769800	BY481P LED250S/840 PSD HRO PC SI	114 °	-	-	-
40793300	BY481P LED350S/840 PSD WB PC SI	114 °	-	-	-
40795700	BY481P LED250S/840 PSD NB PC SI	114 °	-	-	-
40798800	BY481P LED350S/840 PSD MB PC SI	114 °	-	-	-
40799500	BY481P LED350S/840 PSD HRO PC SI	114 °	-	-	-
40733900	BY480P LED130S/840 PSD WB GC SI	114 °	-	-	-
40736000	BY480P LED170S/840 PSD WB GC SI	114 °	-	-	-
40738400	BY480P LED130S/840 PSD MB GC SI	114 °	-	-	-
40739100	BY480P LED170S/840 PSD HRO GC SI	114 °	-	-	-
40742100	BY480P LED130S/840 PSD HRO GC SI	114 °	-	-	-
40745200	BY480P LED170S/840 PSD MB GC SI	114 °	-	-	-
40785800	BY480P LED130S/840 PSD NB GC SI	114 °	-	-	-
40828200	BY480P LED170S/865 PSD WB GC SI	40 x 40 °	-	-	-
01089500	BY480P LED130S/865 PSD WB GC SI	40 x 40 °	-	-	-
01090100	BY482P LED170S/840 PSD WB GC SI	40 x 40 °	-	-	-
01092500	BY480P LED130S/840 PSD WB GC SI XT	40 x 40 °	-	-	-
01093200	BY480P LED170S/840 PSD WB GC SI XT	40 x 40 °	-	-	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	114 °	-	-	-
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	114 °	-	-	-
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	114 °	-	-	-
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	114 °	-	-	-
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	114 °	-	-	-
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	114 °	-	-	-

Order Code	Full Product Name	Beam angle of light source	Cap base	Optical cover/ lens type	Lamp family code
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	114 °	-	-	-
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	114 °	-	-	-
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	40 x 40 °	-	-	-
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	40 x 40 °	-	-	-
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	40 x 40 °	-	-	-
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	40 x 40 °	-	-	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	114 °	-	-	-
40758200	BY481P LED250S/840 PSD WB GC SI BR	114 °	-	-	-
40778000	BY481P LED250S/840 PSD NB GC SI BR	114 °	-	-	-
40786500	BY481P LED250S/840 PSD HRO GC SI BR	114 °	-	-	-
40790200	BY481P LED350S/840 PSD MB GC SI BR	114 °	-	-	-
40801500	BY481P LED350S/840 PSD WB GC SI BR	114 °	-	-	-
40757500	BY481P LED250S/840 PSD MB GC WH	114 °	-	-	-
40771100	BY481P LED250S/840 PSD MB PC WH	114 °	-	-	-
40777300	BY481P LED250S/840 PSD WB GC WH	114 °	-	-	-
40800800	BY481P LED250S/840 PSD HRO GC WH	114 °	-	-	-
40830500	BY481P LED250S/865 PSD WB GC SI	40 x 40 °	-	-	-
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	40 x 40 °	-	-	-
40892300	BY481P LED250S/840 PSD- CLO WB GC SI	40 x 40 °	-	-	-
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	40 x 40 °	-	-	-
01091800	BY483P LED250S/840 PSD WB GC SI	40 x 40 °	-	-	-
01094900	BY481P LED250S/840 PSD WB GC SI XT	40 x 40 °	-	-	-
01095600	BY481P LED350S/840 PSD WB GC SI XT	40 x 40 °	-	-	-
01102100	BY481P LED250S/840 PSED WB GC SI	40 x 40 °	-	-	-
01103800	BY481P LED250S/840 PSED- CLO WB GC SI	40 x 40 °	-	-	-

GentleSpace Gen3

Order Code	Full Product Name	Beam angle of light source	Cap base	Optical cover/ lens type	Lamp family code
40760500	BY480P LED130S/840 PSD WB GC WH	114 °	-	-	-
40776600	BY480P LED130S/840 PSD MB GC WH	114 °	-	-	-
40766700	BY480P LED130S/840 PSD WB GC SI BR	114 °	-	-	-
40781000	BY481P LED250S/840 PSD MB GC WH BR	114 °	-	-	-
40788900	BY481P LED250S/840 PSD WB GC WH BR	114 °	-	-	-
41152700	BY481P LED350S/865 PSD WB PC SI BR	40 x 40 °	-	-	-
41463400	BY480P LED130S/840 PSD NBA GC SI	114 °	-	PM	-

Order Code	Full Product Name	Beam angle of light source	Cap base	Optical cover/ lens type	Lamp family code
41464100	BY480P LED170S/840 PSD NBA GC SI	114 °	-	PM	-
41465800	BY481P LED250S/840 PSD NBA GC SI	114 °	-	PM	-
41466500	BY481P LED350S/840 PSD NBA GC SI	114 °	-	PM	-
41467200	BY481P LED350S/840 PSD NBA PC SI	114 °	-	PM	-
41468900	BY481P LED250S/840 PSD NBA PC SI	114 °	-	PM	-
41469600	BY480P LED130S/840 PSD NBA PC SI	114 °	-	PM	-
41470200	BY480P LED170S/840 PSD NBA PC SI	114 °	-	PM	-

General Information (2/2)

Order Code	Full Product Name	Optic type	Product family code	UL mark
40730800	BY481P LED250S/840 PSD WB GC SI	WB	BY481P	-
40731500	BY481P LED250S/840 PSD MB GC SI	MB	BY481P	-
40732200	BY481P LED350S/840 PSD MB GC SI	MB	BY481P	-
40734600	BY481P LED250S/840 PSD NB GC SI	NB	BY481P	-
40741400	BY481P LED250S/840 PSD WB PC SI	WB	BY481P	-
40743800	BY481P LED350S/840 PSD WB GC SI	WB	BY481P	-
40744500	BY481P LED250S/840 PSD MB PC SI	MB	BY481P	-
40763600	BY481P LED250S/840 PSD HRO GC SI	HRO	BY481P	-
40767400	BY481P LED350S/840 PSD HRO GC SI	HRO	BY481P	-
40768100	BY481P LED350S/840 PSD NB GC SI	NB	BY481P	-
40769800	BY481P LED250S/840 PSD HRO PC SI	HRO	BY481P	-
40793300	BY481P LED350S/840 PSD WB PC SI	WB	BY481P	-
40795700	BY481P LED250S/840 PSD NB PC SI	NB	BY481P	-
40798800	BY481P LED350S/840 PSD MB PC SI	MB	BY481P	-
40799500	BY481P LED350S/840 PSD HRO PC SI	HRO	BY481P	-
40733900	BY480P LED130S/840 PSD WB GC SI	WB	BY480P	-
40736000	BY480P LED170S/840 PSD WB GC SI	WB	BY480P	-
40738400	BY480P LED130S/840 PSD MB GC SI	MB	BY480P	-
40739100	BY480P LED170S/840 PSD HRO GC SI	HRO	BY480P	-
40742100	BY480P LED130S/840 PSD HRO GC SI	HRO	BY480P	-
40745200	BY480P LED170S/840 PSD MB GC SI	MB	BY480P	-
40785800	BY480P LED130S/840 PSD NB GC SI	NB	BY480P	-
40828200	BY480P LED170S/865 PSD WB GC SI	WB	BY480P	-
01089500	BY480P LED130S/865 PSD WB GC SI	WB	BY480P	-
01090100	BY482P LED170S/840 PSD WB GC SI	WB	BY482P	-
01092500	BY480P LED130S/840 PSD WB GC SI XT	WB	BY480P	-
01093200	BY480P LED170S/840 PSD WB GC SI XT	WB	BY480P	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	MB	BY481X	-
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	WB	BY481X	-

Order Code	Full Product Name	Optic type	Product family code	UL mark
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	HRO	BY481X	-
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	MB	BY481X	-
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	WB	BY481X	-
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	HRO	BY481X	-
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	NB	BY481X	-
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	NB	BY481X	-
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	WB	BY480X	-
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	WB	BY481X	-
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	WB	BY481X	-
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	WB	BY480X	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	MB	BY481P	-
40758200	BY481P LED250S/840 PSD WB GC SI BR	WB	BY481P	-
40778000	BY481P LED250S/840 PSD NB GC SI BR	NB	BY481P	-
40786500	BY481P LED250S/840 PSD HRO GC SI BR	HRO	BY481P	-
40790200	BY481P LED350S/840 PSD MB GC SI BR	MB	BY481P	-
40801500	BY481P LED350S/840 PSD WB GC SI BR	WB	BY481P	-
40757500	BY481P LED250S/840 PSD MB GC WH	MB	BY481P	-
40771100	BY481P LED250S/840 PSD MB PC WH	MB	BY481P	-
40777300	BY481P LED250S/840 PSD WB GC WH	WB	BY481P	-
40800800	BY481P LED250S/840 PSD HRO GC WH	HRO	BY481P	-

Order Code	Full Product Name	Optic type	Product family code	UL mark
40830500	BY481P LED250S/865 PSD WB GC SI	WB	BY481P	-
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	WB	BY481P	-
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	WB	BY481P	-
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	WB	BY481P	-
01091800	BY483P LED250S/840 PSD WB GC SI	WB	BY483P	-
01094900	BY481P LED250S/840 PSD WB GC SI XT	WB	BY481P	-
01095600	BY481P LED350S/840 PSD WB GC SI XT	WB	BY481P	-
01102100	BY481P LED250S/840 PSED WB GC SI	WB	BY481P	-
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	WB	BY481P	-
40760500	BY480P LED130S/840 PSD WB GC WH	WB	BY480P	-
40776600	BY480P LED130S/840 PSD MB GC WH	MB	BY480P	-

Order Code	Full Product Name	Optic type	Product family code	UL mark
40766700	BY480P LED130S/840 PSD WB GC SI BR	WB	BY480P	-
40781000	BY481P LED250S/840 PSD MB GC WH BR	WB	BY481P	-
40788900	BY481P LED250S/840 PSD WB GC WH BR	WB	BY481P	-
41152700	BY481P LED350S/865 PSD WB PC SI BR	WB	BY481P	-
41463400	BY480P LED130S/840 PSD NBA GC SI	WB	BY480P	-
41464100	BY480P LED170S/840 PSD NBA GC SI	WB	BY480P	-
41465800	BY481P LED250S/840 PSD NBA GC SI	WB	BY481P	-
41466500	BY481P LED350S/840 PSD NBA GC SI	WB	BY481P	-
41467200	BY481P LED350S/840 PSD NBA PC SI	WB	BY481P	-
41468900	BY481P LED250S/840 PSD NBA PC SI	WB	BY481P	-
41469600	BY480P LED130S/840 PSD NBA PC SI	WB	BY480P	-
41470200	BY480P LED170S/840 PSD NBA PC SI	WB	BY480P	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40730800	BY481P LED250S/840 PSD WB GC SI	4000 K	154 lm/W	25000 lm	160 W
40731500	BY481P LED250S/840 PSD MB GC SI	4000 K	154 lm/W	25000 lm	160 W
40732200	BY481P LED350S/840 PSD MB GC SI	4000 K	148 lm/W	35000 lm	230 W
40734600	BY481P LED250S/840 PSD NB GC SI	4000 K	154 lm/W	25000 lm	160 W
40741400	BY481P LED250S/840 PSD WB PC SI	4000 K	154 lm/W	25000 lm	160 W
40743800	BY481P LED350S/840 PSD WB GC SI	4000 K	148 lm/W	35000 lm	230 W
40744500	BY481P LED250S/840 PSD MB PC SI	4000 K	154 lm/W	25000 lm	160 W
40763600	BY481P LED250S/840 PSD HRO GC SI	4000 K	154 lm/W	25000 lm	160 W
40767400	BY481P LED350S/840 PSD HRO GC SI	4000 K	148 lm/W	35000 lm	230 W
40768100	BY481P LED350S/840 PSD NB GC SI	4000 K	148 lm/W	35000 lm	230 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40769800	BY481P LED250S/840 PSD HRO PC SI	4000 K	154 lm/W	25000 lm	160 W
40793300	BY481P LED350S/840 PSD WB PC SI	4000 K	148 lm/W	35000 lm	230 W
40795700	BY481P LED250S/840 PSD NB PC SI	4000 K	154 lm/W	25000 lm	160 W
40798800	BY481P LED350S/840 PSD MB PC SI	4000 K	148 lm/W	35000 lm	230 W
40799500	BY481P LED350S/840 PSD HRO PC SI	4000 K	148 lm/W	35000 lm	230 W
40733900	BY480P LED130S/840 PSD WB GC SI	4000 K	153 lm/W	13000 lm	84 W
40736000	BY480P LED170S/840 PSD WB GC SI	4000 K	142 lm/W	17000 lm	120 W
40738400	BY480P LED130S/840 PSD MB GC SI	4000 K	153 lm/W	13000 lm	84 W
40739100	BY480P LED170S/840 PSD HRO GC SI	4000 K	142 lm/W	17000 lm	120 W
40742100	BY480P LED130S/840 PSD HRO GC SI	4000 K	153 lm/W	13000 lm	84 W

GentleSpace Gen3

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40745200	BY480P LED170S/840 PSD MB GC SI	4000 K	142 lm/W	17000 lm	120 W
40785800	BY480P LED130S/840 PSD NB GC SI	4000 K	153 lm/W	13000 lm	84 W
40828200	BY480P LED170S/865 PSD WB GC SI	6500 K	142 lm/W	17000 lm	120 W
01089500	BY480P LED130S/865 PSD WB GC SI	6500 K	153 lm/W	13000 lm	84 W
01090100	BY482P LED170S/840 PSD WB GC SI	4000 K	142 lm/W	17000 lm	120 W
01092500	BY480P LED130S/840 PSD WB GC SI XT	4000 K	153 lm/W	13000 lm	84 W
01093200	BY480P LED170S/840 PSD WB GC SI XT	4000 K	142 lm/W	17000 lm	120 W
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	4000 K	154 lm/W	25000 lm	160 W
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	4000 K	154 lm/W	25000 lm	160 W
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	4000 K	154 lm/W	25000 lm	160 W
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	4000 K	148 lm/W	35000 lm	230 W
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	4000 K	148 lm/W	35000 lm	230 W
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	4000 K	148 lm/W	35000 lm	230 W
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	4000 K	154 lm/W	25000 lm	160 W
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	4000 K	148 lm/W	35000 lm	230 W
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	4000 K	142 lm/W	17000 lm	120 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	4000 K	154 lm/W	25000 lm	160 W
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	4000 K	148 lm/W	35000 lm	230 W
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	4000 K	153 lm/W	13000 lm	84 W
40750600	BY481P LED250S/840 PSD MB GC SI BR	4000 K	154 lm/W	25000 lm	160 W
40758200	BY481P LED250S/840 PSD WB GC SI BR	4000 K	154 lm/W	25000 lm	160 W
40778000	BY481P LED250S/840 PSD NB GC SI BR	4000 K	154 lm/W	25000 lm	160 W
40786500	BY481P LED250S/840 PSD HRO GC SI BR	4000 K	154 lm/W	25000 lm	160 W
40790200	BY481P LED350S/840 PSD MB GC SI BR	4000 K	148 lm/W	35000 lm	230 W
40801500	BY481P LED350S/840 PSD WB GC SI BR	4000 K	148 lm/W	35000 lm	230 W
40757500	BY481P LED250S/840 PSD MB GC WH	4000 K	154 lm/W	25000 lm	160 W
40771100	BY481P LED250S/840 PSD MB PC WH	4000 K	154 lm/W	25000 lm	160 W
40777300	BY481P LED250S/840 PSD WB GC WH	4000 K	154 lm/W	25000 lm	160 W
40800800	BY481P LED250S/840 PSD HRO GC WH	4000 K	154 lm/W	25000 lm	160 W
40830500	BY481P LED250S/865 PSD WB GC SI	6500 K	154 lm/W	25000 lm	160 W
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	4000 K	148 lm/W	35000 lm	230 W
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	4000 K	154 lm/W	25000 lm	160 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	4000 K	148 lm/W	35000 lm	230 W
01091800	BY483P LED250S/840 PSD WB GC SI	4000 K	154 lm/W	25000 lm	160 W
01094900	BY481P LED250S/840 PSD WB GC SI XT	4000 K	154 lm/W	25000 lm	160 W
01095600	BY481P LED350S/840 PSD WB GC SI XT	4000 K	148 lm/W	35000 lm	230 W
01102100	BY481P LED250S/840 PSED WB GC SI	4000 K	154 lm/W	25000 lm	160 W
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	4000 K	154 lm/W	25000 lm	160 W
40760500	BY480P LED130S/840 PSD WB GC WH	4000 K	153 lm/W	13000 lm	84 W
40776600	BY480P LED130S/840 PSD MB GC WH	4000 K	153 lm/W	13000 lm	84 W
40766700	BY480P LED130S/840 PSD WB GC SI BR	4000 K	153 lm/W	13000 lm	84 W
40781000	BY481P LED250S/840 PSD MB GC WH BR	4000 K	154 lm/W	25000 lm	160 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40788900	BY481P LED250S/840 PSD WB GC WH BR	4000 K	154 lm/W	25000 lm	160 W
41152700	BY481P LED350S/865 PSD WB PC SI BR	6500 K	148 lm/W	35000 lm	230 W
41463400	BY480P LED130S/840 PSD NBA GC SI	4000 K	153 lm/W	13000 lm	84 W
41464100	BY480P LED170S/840 PSD NBA GC SI	4000 K	142 lm/W	17000 lm	120 W
41465800	BY481P LED250S/840 PSD NBA GC SI	4000 K	154 lm/W	25000 lm	160 W
41466500	BY481P LED350S/840 PSD NBA GC SI	4000 K	148 lm/W	35000 lm	230 W
41467200	BY481P LED350S/840 PSD NBA PC SI	4000 K	148 lm/W	35000 lm	230 W
41468900	BY481P LED250S/840 PSD NBA PC SI	4000 K	154 lm/W	25000 lm	160 W
41469600	BY480P LED130S/840 PSD NBA PC SI	4000 K	153 lm/W	13000 lm	84 W
41470200	BY480P LED170S/840 PSD NBA PC SI	4000 K	142 lm/W	17000 lm	120 W

Mechanical and Housing

Order Code	Full Product Name	Colour	Diameter
40730800	BY481P LED250S/840 PSD WB GC SI	Silver	-
40731500	BY481P LED250S/840 PSD MB GC SI	Silver RAL 9006	-
40732200	BY481P LED350S/840 PSD MB GC SI	Silver RAL 9006	-
40734600	BY481P LED250S/840 PSD NB GC SI	Silver RAL 9006	-
40741400	BY481P LED250S/840 PSD WB PC SI	Silver RAL 9006	-
40743800	BY481P LED350S/840 PSD WB GC SI	Silver RAL 9006	-
40744500	BY481P LED250S/840 PSD MB PC SI	Silver RAL 9006	-
40763600	BY481P LED250S/840 PSD HRO GC SI	Silver RAL 9006	-
40767400	BY481P LED350S/840 PSD HRO GC SI	Silver RAL 9006	-
40768100	BY481P LED350S/840 PSD NB GC SI	Silver RAL 9006	-
40769800	BY481P LED250S/840 PSD HRO PC SI	Silver RAL 9006	-
40793300	BY481P LED350S/840 PSD WB PC SI	Silver RAL 9006	-
40795700	BY481P LED250S/840 PSD NB PC SI	Silver RAL 9006	-
40798800	BY481P LED350S/840 PSD MB PC SI	Silver RAL 9006	-
40799500	BY481P LED350S/840 PSD HRO PC SI	Silver RAL 9006	-

Order Code	Full Product Name	Colour	Diameter
40733900	BY480P LED130S/840 PSD WB GC SI	Silver RAL 9006	-
40736000	BY480P LED170S/840 PSD WB GC SI	Silver RAL 9006	-
40738400	BY480P LED130S/840 PSD MB GC SI	Silver RAL 9006	-
40739100	BY480P LED170S/840 PSD HRO GC SI	Silver RAL 9006	-
40742100	BY480P LED130S/840 PSD HRO GC SI	Silver RAL 9006	-
40745200	BY480P LED170S/840 PSD MB GC SI	Silver RAL 9006	-
40785800	BY480P LED130S/840 PSD NB GC SI	Silver RAL 9006	-
40828200	BY480P LED170S/865 PSD WB GC SI	Silver RAL 9006	-
01089500	BY480P LED130S/865 PSD WB GC SI	Silver RAL 9006	-
01090100	BY482P LED170S/840 PSD WB GC SI	Silver RAL 9006	-
01092500	BY480P LED130S/840 PSD WB GC SI XT	Silver RAL 9006	-
01093200	BY480P LED170S/840 PSD WB GC SI XT	Silver RAL 9006	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	Silver RAL 9006	-
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	Silver RAL 9006	-
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	Silver RAL 9006	-

GentleSpace Gen3

Order Code	Full Product Name	Colour	Diameter
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	Silver RAL 9006	-
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	Silver RAL 9006	-
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	Silver RAL 9006	-
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	Silver RAL 9006	-
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	Silver RAL 9006	-
40829900	BY480X LED170S/840 WB GC SI ACW-W BR	Silver RAL 9006	-
40833600	BY481X LED250S/840 WB GC SI ACW-W BR	Silver RAL 9006	-
40834300	BY481X LED350S/840 WB GC SI ACW-W BR	Silver RAL 9006	-
01101400	BY480X LED130S/840 WB GC SI ACW-W BR	Silver RAL 9006	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	Silver RAL 9006	-
40758200	BY481P LED250S/840 PSD WB GC SI BR	Silver RAL 9006	-
40778000	BY481P LED250S/840 PSD NB GC SI BR	Silver RAL 9006	-
40786500	BY481P LED250S/840 PSD HRO GC SI BR	Silver RAL 9006	-
40790200	BY481P LED350S/840 PSD MB GC SI BR	Silver RAL 9006	-
40801500	BY481P LED350S/840 PSD WB GC SI BR	Silver RAL 9006	-
40757500	BY481P LED250S/840 PSD MB GC WH	White	-
40771100	BY481P LED250S/840 PSD MB PC WH	White	-
40777300	BY481P LED250S/840 PSD WB GC WH	White	-
40800800	BY481P LED250S/840 PSD HRO GC WH	White	-
40830500	BY481P LED250S/865 PSD WB GC SI	Silver RAL 9006	-
40832900	BY481P LED350S/840 PSD WB GC SI ELD3	Silver RAL 9006	-

Order Code	Full Product Name	Colour	Diameter
40892300	BY481P LED250S/840 PSD-CLO WB GC SI	Silver RAL 9006	-
40925800	BY481P LED350S/840 PSD WB GC SI ELP3	Silver RAL 9006	-
01091800	BY483P LED250S/840 PSD WB GC SI	Silver RAL 9006	-
01094900	BY481P LED250S/840 PSD WB GC SI XT	Silver RAL 9006	-
01095600	BY481P LED350S/840 PSD WB GC SI XT	Silver RAL 9006	-
01102100	BY481P LED250S/840 PSED WB GC SI	Silver RAL 9006	-
01103800	BY481P LED250S/840 PSED-CLO WB GC SI	Silver RAL 9006	-
40760500	BY480P LED130S/840 PSD WB GC WH	White	-
40776600	BY480P LED130S/840 PSD MB GC WH	White	-
40766700	BY480P LED130S/840 PSD WB GC SI BR	Silver RAL 9006	-
40781000	BY481P LED250S/840 PSD MB GC WH BR	White	-
40788900	BY481P LED250S/840 PSD WB GC WH BR	White	-
41152700	BY481P LED350S/865 PSD WB PC SI BR	Silver RAL 9006	-
41463400	BY480P LED130S/840 PSD NBA GC SI	Silver RAL 9006	-
41464100	BY480P LED170S/840 PSD NBA GC SI	Silver RAL 9006	-
41465800	BY481P LED250S/840 PSD NBA GC SI	Silver RAL 9006	-
41466500	BY481P LED350S/840 PSD NBA GC SI	Silver RAL 9006	-
41467200	BY481P LED350S/840 PSD NBA PC SI	Silver RAL 9006	-
41468900	BY481P LED250S/840 PSD NBA PC SI	Silver RAL 9006	-
41469600	BY480P LED130S/840 PSD NBA PC SI	Silver RAL 9006	-
41470200	BY480P LED170S/840 PSD NBA PC SI	Silver RAL 9006	-

