



# GentleSpace Gen3

## BY481X LED350S/840 WB GC SI ACW-W BR

New Highbay - 840 neutral white - Power supply unit with DALI interface - Wide beam - Silver RAL 9006

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

### Product data

General Information			
Beam angle of light source	40 x 40 °	Control interface	DALI
Light source colour	840 neutral white	Connection	CE [ External connector]
Light source replaceable	Yes	Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of gear units	1 unit	Protection class IEC	Safety class I (I)
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Glow-wire test	850/5 [ Temperature 850 °C, duration 5 s]
Driver included	Yes	Flammability mark	D [ For mounting on easily flammable surfaces]
Optic type	WB [ Wide beam]	CE mark	CE mark
Luminaire light beam spread	42° x 44°	ENEC mark	ENEC mark

# GentleSpace Gen3

Warranty period	5 years
Constant light output	No
Number of products on MCB (16 A type B)	8
EU RoHS compliant	Yes
Product family code	BY481X [ New Highbay]
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	232 W
Inrush current	15.3 A
Inrush time	0.061 ms
Power factor (min.)	0.9

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	712 mm
Overall width	490 mm
Overall height	120 mm
Colour	Silver RAL 9006
Dimensions (height x width x depth)	120 x 490 x 712 mm (4.7 x 19.3 x 28 in)

## Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK02 [ 0.2 J standard]

## Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	35000 lm
Luminous flux tolerance	+/-10%

Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	230 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 75,000 h	L80
Lumen maintenance at median useful life* 100,000 h	L80

## Application Conditions

Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	45 °C
Maximum dimming level	10%
Suitable for random switching	Yes


## Product Data

Full product code	871869940834300
Order product name	BY481X LED350S/840 WB GC SI ACW-W BR
EAN/UPC – product	8718699408343
Order code	40834300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910500465619
SAP net weight (piece)	11.000 kg




# GentleSpace Gen3

## Dimensional drawing




GentleSpace gen3 BY480P-BY483P

## Photometric data



IFGU1\_BY481XACW1xLED350S840WB



OFPC1\_BY481XACW1xLED350S840WB

