



GentleSpace Gen3

BY481P LED350S/840 PSD NBA PC SI

New Highbay - 840 neutral white - Power supply unit with DALI interface - Narrow beam adjustable - PMMA bowl/cover - Silver RAL 9006

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

Product data

General Information	
Lamp family code	-
Beam angle of light source	114 °
Light source colour	840 neutral white
Cap base	- [-]
Light source replaceable	Yes
Number of gear units	1 unit

Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	Narrow beam adjustable
Optical cover/lens type	PM [PMMA bowl/cover]
Luminaire light beam spread	25° x 30°
Control interface	DALI
Connection	CE [External connector]

GentleSpace Gen3

Cable	Cord with plug Wieland/Adels compatible 5-pole
Protection class IEC	Safety class I (I)
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Constant light output	No
Number of products on MCB (16 A type B)	8
Photobiological risk	Photobiological risk group 2 @ 200mm to EN62471
Photobiological risk specification	8.4 m
EU RoHS compliant	Yes
Product family code	BY481P [New Highbay]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	15.3 A
Inrush time	6.1 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	600 mm
Overall width	490 mm
Overall height	110 mm
Diameter	-
Colour	Silver RAL 9006
Dimensions (height x width x depth)	110 x 490 x 600 mm (4.3 x 19.3 x 23.6 in)

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	35000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	150 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	232 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	45 °C
Maximum dimming level	10%
Suitable for random switching	No


Product Data

Full product code	871869941467200
Order product name	BY481P LED350S/840 PSD NBA PC SI
EAN/UPC – product	8718699414672
Order code	41467200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910500465805
SAP net weight (piece)	11.000 kg




GentleSpace Gen3

Dimensional drawing




BY481P LED350S/840 PSD NBA PC SI


Photometric data




OFPC1_



IFGU1_



OFPC1_BY481PPSD1xLED350S840NBA-NB



IFGU1_BY481PPSD1xLED350S840NBA-NB

GentleSpace Gen3

