



# TownGuide Performer

## BDP100 LED40/830 II DM PCC SI CLO-LS-6 6

TOWNGUIDE PERF FLAT CONE - LED module 4000 lm -  
Distribution medium - Polycarbonate bowl/cover clear

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

### Product data

General information			
Number of light sources	4 [ 4 pcs]	Driver included	Yes
Lamp family code	LED40 [ LED module 4000 lm]	Optical cover/lens type	PCC [ Polycarbonate bowl/cover clear]
Light source colour	830 warm white	Luminaire light beam spread	53° x 71°
Light source replaceable	Yes	Embedded control	CLO-LS-6 [ Constant light output and LumiStep dimming 6 hours]
Number of gear units	1 unit	Control interface	-
Driver/power unit/transformer	PSDD-CLO [ Power supply unit with DynaDimmer and constant light output (integrated)]	Light regulation	Dimming via DynaDimmer integrated in ballast or driver
		Connection	Screw connection block 5-pole

# TownGuide Performer

Cable	-
Protection class IEC	Safety class II (II)
Parts colour	All parts colored
Coating	-
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Flammability mark	NO [ -]
Safety device	PCBC [ PCB cover]
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years
Optic type outdoor	Distribution medium
Photocell	No [ -]
Constant light output	Yes
Number of products on MCB (16 A type B)	10
EU RoHS compliant	Yes
WEEE mark	-
Light source engine type	LED
Service Tag	Yes
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BDP100 [ TOWNGUIDE PERF FLAT CONE]

## Light technical

Upward light output ratio	3
Standard tilt angle post-top	0°
Standard tilt angle side entry	-

## Operating and electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	30.5 W
Average CLO power consumption	31.5 W
End CLO power consumption	32.5 W
Inrush current	45 A
Inrush time	0.285 ms
Power factor (min.)	0.94
Power factor (nom.)	0.81

## Controls and dimming

Dimmable	Yes
----------	-----

## Mechanical and housing

Housing material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Mounting device	62P [ Post-top for diameter 62 mm]
Optical cover/lens shape	Conical flat

Optical cover/lens finish	Clear
Torque	15
Overall height	209 mm
Overall diameter	570 mm
Effective projected area	0.051 m <sup>2</sup>
Colour	Silver
Dimensions (height x width x depth)	209 x NaN x NaN mm

## Approval and application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Surge protection (common/differential)	Luminaire surge protection level up to 6 kV differential mode and 6 kV common mode
Sustainability rating	-

## Initial performance (IEC compliant)

Initial luminous flux (system flux)	2888 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	95 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	80
Initial chromaticity	(0.43, 0.40) SDCM <5
Initial input power	32.5 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

## Over time performance (IEC compliant)

Driver failure rate at 5,000 hours	0.5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	94

## Application conditions

Ambient temperature range	-40 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	50%


## Product data

Full product code	871829190609400
Order product name	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6
EAN/UPC – product	8718291906094
Order code	90609400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910500991010
Net Weight (Piece)	6.380 kg



## TownGuide Performer

### Dimensional drawing



BDP100 LED40/830 II DM PCC SI CLO-LS-6 6

