



TownGuide Performer

BDP101 LED60/830 II DS PCF SI CLO-DDF2 6

TOWNGUIDE PERF BOWL - LED module 6000 lm - Distribution symmetrical - Polycarbonate bowl/cover frosted

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

Product data

| General information | | | |
|-------------------------------|--|-----------------------------|--|
| Number of light sources | 8 [8 pcs] | Driver included | Yes |
| Lamp family code | LED60 [LED module 6000 lm] | Optical cover/lens type | PCF [Polycarbonate bowl/cover frosted] |
| Light source colour | 830 warm white | Luminaire light beam spread | 75° |
| Light source replaceable | Yes | Embedded control | CLO-DDF2 [Constant light output and DynaDimmer fixed presets version 2] |
| Number of gear units | 1 unit | Control interface | - |
| Driver/power unit/transformer | PSDD-CLO [Power supply unit with DynaDimmer and constant light output (integrated)] | Light regulation | Dimming via DynaDimmer integrated in ballast or driver |
| | | Connection | Screw connection block 5-pole |

TownGuide Performer

| | |
|---|--|
| Cable | - |
| Protection class IEC | Safety class II (II) |
| Parts colour | All parts colored |
| Coating | - |
| Glow-wire test | 650/5 [Temperature 650 °C, duration 5 s] |
| Flammability mark | NO [-] |
| Safety device | PCBC [PCB cover] |
| CE mark | CE mark |
| ENEC mark | ENEC mark |
| Warranty period | 5 years |
| Optic type outdoor | Distribution symmetrical |
| Photocell | No [-] |
| Constant light output | Yes |
| Number of products on MCB (16 A type B) | 10 |
| EU RoHS compliant | Yes |
| WEEE mark | - |
| Light source engine type | LED |
| Serviceability class | Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts |
| Product family code | BDP101 [TOWNGUIDE PERF BOWL] |

Light technical

| | |
|--------------------------------|----|
| Upward light output ratio | 15 |
| Standard tilt angle post-top | 0° |
| Standard tilt angle side entry | - |

Operating and electrical

| | |
|-------------------------------|-------------|
| Input Voltage | 220–240 V |
| Input frequency | 50 to 60 Hz |
| Initial CLO power consumption | 37 W |
| Average CLO power consumption | 38.5 W |
| End CLO power consumption | 40 W |
| Inrush current | 45 A |
| Inrush time | 0.285 ms |
| Power factor (min.) | 0.95 |
| Power factor (nom.) | 0.88 |

Controls and dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Mechanical and housing

| | |
|-----------------------------|------------------------------------|
| Housing material | Aluminum |
| Reflector material | - |
| Optic material | Acrylate |
| Optical cover/lens material | Polycarbonate |
| Fixation material | Steel |
| Mounting device | 62P [Post-top for diameter 62 mm] |
| Optical cover/lens shape | Hemispherical |

| | |
|-------------------------------------|----------------------|
| Optical cover/lens finish | Frosted |
| Torque | 15 |
| Overall height | 293 mm |
| Overall diameter | 570 mm |
| Effective projected area | 0.095 m ² |
| Colour | Silver |
| Dimensions (height x width x depth) | 293 x NaN x NaN mm |

Approval and application

| | |
|--|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK10 [20 J vandal-resistant] |
| Surge protection (common/differential) | Luminaire surge protection level up to 6 kV differential mode and 6 kV common mode |
| Sustainability rating | - |

Initial performance (IEC compliant)

| | |
|--|----------------------|
| Initial luminous flux (system flux) | 2300 lm |
| Luminous flux tolerance | +/-7% |
| Initial LED luminaire efficacy | 62 lm/W |
| Init. Corr. Colour Temperature | 3000 K |
| Init. Colour rendering index | 80 |
| Initial chromaticity | (0.43, 0.40) SDCM <5 |
| Initial input power | 40 W |
| Power consumption tolerance | +/-10% |
| Init. colour rendering index tolerance | +/-2 |

Over time performance (IEC compliant)

| | |
|---|-------|
| Driver failure rate at 5,000 hours | 0.5 % |
| Control gear failure rate at median useful life 100,000 h | 10 % |
| Lumen maintenance at median useful life* 100,000 h | 94 |

Application conditions

| | |
|------------------------------------|---------------|
| Ambient temperature range | -40 to +35 °C |
| Performance ambient temperature Tq | 25 °C |
| Maximum dimming level | 50% |

Product data

| | |
|-----------------------------------|--|
| Full product code | 871829190614800 |
| Order product name | BDP101 LED60/830 II DS PCF SI CLO-DDF2 6 |
| EAN/UPC – product | 8718291906148 |
| Order code | 90614800 |
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| SAP material | 910500991015 |
| Net Weight (Piece) | 6.830 kg |



TownGuide Performer

Dimensional drawing



BDP101 LED60/830 II DS PCF SI CLO-DDF2 6

