



Maxos, mounting accessories

9MX056 CB SI

Chain bracket

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Product data

| General Information | | Operating and Electrical | |
|-----------------------------------|---------------------|-------------------------------------|---|
| Protection class IEC | - | Electrical accessories | No [-] |
| Suspension accessories | CB [Chain bracket] | Circuit | No [-] |
| Mechanical accessories | No [-] | Mechanical and Housing | |
| Packaging configuration | No [-] | Length | - mm |
| Accessory colour | Silver | Dimensions (height x width x depth) | NaN x NaN x NaN mm (NaN x NaN x NaN in) |
| Emergency lighting accessories | No [-] | Approval and Application | |
| Product family code | 9MX056 [ACC MAXOS] | Ingress protection code | - [-] |
| Light Technical | | Product Data | |
| Optical cover/lens type accessory | No [-] | Full product code | 403073255676299 |

Maxos, mounting accessories

| | |
|-----------------------------------|---------------|
| Order product name | 9MX056 CB SI |
| EAN/UPC – product | 4030732556762 |
| Order code | 55676299 |
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 6 |

| | |
|------------------------|--------------|
| SAP material | 910680017426 |
| SAP net weight (piece) | 0.050 kg |

