

Green Perform Highbay Elite

BY718P LED100/NW PSD WB

Power supply unit with DALI interface - Symmetrical - Polycarbonate bowl/cover - 90°

GreenPerform Highbay Elite is the latest innovation in a successful range of highbay luminaires for high ceiling and industrial applications. The unique finless design has received the iF Design Award 2019 and Reddot Design Award 2019 for its aesthetic appeal. But this versatile luminaire offers a wealth of practical features too, including great light quality, high energy savings, a long lifetime at an affordable price and a wide variety of optics and lumen packages. The Green Perform Highbay Elite luminaire provides options for advanced connectivity with IoT-based systems and software applications including the Interact Pro system. If you're looking for a 'fit and forget' robust and reliable solution with connectivity advantages, Green Perform Highbay Elite is the smart choice.

Product data


General information	
Light source colour	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	Symmetrical
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	90°
Control interface	DALI
Cable	Cable 0.3 m without plug

Protection class IEC	Safety class I (I)
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
Number of products on MCB (16 A type B)	8
EU RoHS compliant	Yes


Green Perform Highbay Elite

Light source engine type	LED
Operating and electrical	
Input Voltage	220 to 240 V
Input frequency	50 or 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power factor (min.)	0.95
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Optical cover/lens finish	Frosted
Overall height	445 mm
Overall diameter	385 mm
Colour	Black and gray
Approval and application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	11000 lm

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	145 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial input power	73 W
Power consumption tolerance	+/-10%
Over time performance (IEC compliant)	
Driver failure rate at 5,000 hours	0.0021 %
Median useful life L70B50	75000 h
Application conditions	
Ambient temperature range	-30 to +50 °C
Maximum dimming level	1%
Suitable for random switching	No
Product data	
Full product code	911401572151
Order product name	BY718P LED100/NW PSD WB
Order code	01572151
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	911401572151
Net Weight (Piece)	6.000 kg



Dimensional drawing



BY718P LED100/NW PSD WB

Green Perform Highbay Elite

