



GreenPerform Trunking

LL120X LED140 L3000 NW PSU 5 DA ENG

LED module 15200 lm - Neutral white - Power supply unit - Double asymmetric optic

With Philips GreenPerform Trunking, industry and supermarket owners have an innovative LED solution that intelligently combines high-performance lighting features with maximised energy savings. This solution is designed to boost productivity and enhance the shopping experience without compromising performance and energy-efficiency. Suitable for a wide range of applications, GreenPerform Trunking is safe, reliable and versatile, the perfect direct replacement for conventional fluorescent trunking.

Product data

General Information			
Lamp family code	LED152 [LED module 15200 lm]	Connection	CI [Internal connector]
Beam angle of light source	90 x 90 °	Cable	-
Light source colour	Neutral white	Protection class IEC	Safety class I (I)
Light source replaceable	No	Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]
Number of gear units	2 units	Flammability mark	NO [-]
Gear	-	CE mark	CE mark
Driver/power unit/transformer	PSU [Power supply unit]	ENEC mark	-
Driver included	Yes	UL mark	-
Optic type	DA [Double asymmetric optic]	Warranty period	3 years
Optical cover/lens type	LIN-PC [Linear-lens array in polycarbonate cover]	Constant light output	Yes
Luminaire light beam spread	100°	Spare parts available	No
Control interface	-	Number of products on MCB (16 A type B)	12
		EU RoHS compliant	Yes

GreenPerform Trunking

Light source engine type	LED
--------------------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	140 W
Average CLO power consumption	140 W
Inrush current	38 A
Inrush time	0.275 ms
Power factor (min.)	0.9
Power factor (nom.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Gear tray material	Steel
Fixation material	Stainless steel
Optical cover/lens finish	Clear
Overall length	3000 mm
Overall width	79 mm
Overall height	83 mm
Colour	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	15200 lm
Luminous flux tolerance	+/-7.5%
Initial LED luminaire efficacy	108.57 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	80
Initial chromaticity	(0.38, 0.38) SDCM <5
Initial input power	140 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50000 h
Median useful life L80B50	40000 h
Median useful life L90B50	20000 h

Application Conditions


Ambient temperature range	-20 to +35 °C
Suitable for random switching	No

Product Data

Full product code	911401584721
Order product name	LL120X LED140 L3000 NW PSU 5 DA ENG
Order code	01584721
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	911401584721
SAP net weight (piece)	6.799 kg



Dimensional drawing



GreenPerform electr. units LL120X

GreenPerform Trunking

