



# Dynalite Leading Edge Dimmers

## DDLE801

8 channel Leading Edge Dimmer Controller at 1 A per channel


The Philips Dynalite DDLE801 supports eight channels of leading edge dimming at 1 A per channel. - It is suitable for use with incandescent lighting, as well as leading edge compatible magnetic and electronic transformers. - Advanced LED dimming technology makes the unit particularly suited to residential, retail and hospitality applications. - Active Load technology on each channel Soft start and voltage regulation technologies Superior internal drive componentry tuning Flexible mounting solution

### Product data

General Information		Order product name	DDLE801
CE mark	CE mark	EAN/UPC – product	8718696001363
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	00136300
EU RoHS compliant	Yes	SAP numerator – quantity per pack	1
		Numerator – packs per outer box	1
		SAP material	913703061509
		SAP net weight (piece)	633.000 g
Application Conditions			
Ambient temperature range	-5 to +40 °C		
Product Data			
Full product code	871869600136300		

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers

