



# Plusline Large

## Plusline L 1500W R7s 230V 1CT/10

Mains-voltage linear lamp giving white halogen light

### Product data

General Information	
Cap base	R7S [ R7s]
Operating position	P4 [ Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h
Light Technical	
Luminous flux (nom.)	33000 lm
Luminous flux (rated) (nom.)	33000 lm
Correlated Colour Temperature (Nom)	2900 K
Luminous efficacy (rated) (nom.)	22 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	1500.0 W
Lamp current (nom.)	6.52 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T11 [ T 11mm]
Approval and Application	
Energy consumption kWh/1,000 hours	1500 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790080857500
Order product name	Plusline L 1500W R7s 230V 1CT/10
EAN/UPC – product	8727900808575
Order code	80857500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	923932243241
SAP net weight (piece)	0.020 kg
ILCOS code	HDG//RS-1500-230-R7s-250.7

## Plusline Large

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

Plusline L 1500W R7s 230V 1CT/10

