



# Halogen Clickline G9

## Halogen MV Caps 28W G9 230V CL 1BC/10

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data

General Information	
Cap base	G9 [ G9]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h

Light Technical	
Luminous flux (nom.)	370 lm
Luminous flux (rated) (nom.)	370 lm
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	12.1 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and Electrical	
Power (Rated) (Nom)	28.0 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T13 [ T 13 mm]


Approval and Application	
Energy consumption kWh/1,000 hours	28 kWh

Luminaire Design Requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	350 °C

Product Data	
Full product code	872790025287325
Order product name	Halogen MV Caps 28W G9 230V CL 1BC/10
EAN/UPC – product	8727900252873
Order code	25287325
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	925640644202
SAP net weight (piece)	3.300 g

## Halogen Clickline G9

### Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Caps 28W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm

CLICKLINE 28W G9 230V CL

