



MASTER PL-L 4 Pin

MASTER PL-L 24W/830/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information		Light technical	
Cap base	2G11 [2G11]	LSF preheat 4,000 hours rated	99 %
Life to 10% failures (nom.)	10000 h	LSF preheat 6,000 hours rated	98 %
Life to 50% failures (nom.)	15000 h	LSF preheat 8,000 hours rated	97 %
Life to 50% failures preheat (nom.)	20000 h	LSF preheat 16,000 hours rated	82 %
System description	na [-]	LSF preheat 20,000 hours rated	50 %
LSF 2000 h Rated	99 %		Sphere
LSF 4000 h Rated	98 %		
LSF 6000 h Rated	96 %		
LSF 8000 h Rated	94 %		
LSF 12000 h Rated	80 %		
LSF preheat 2,000 hours rated	99 %		
		Colour Code	830 [CCT of 3,000 K]
		Luminous flux (nom.)	1800 lm
		Luminous flux (rated) (nom.)	1800 lm
		Colour designation	Warm White (WW)

MASTER PL-L 4 Pin

Chromaticity coordinate X (nom.)	0.44
Chromaticity coordinate Y (nom.)	0.403
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	75 lm/W
Colour rendering index (nom.)	82
LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	93 %
LLMF 6000 h Rated	92 %
LLMF 8000 h Rated	91 %
LLMF 12000 h Rated	90 %
LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	90 %

Operating and electrical

Power (Rated) (Nom)	24.2 W
Lamp current (nom.)	0.345 A

Temperature

Design temperature (nom.)	30 °C
---------------------------	-------

Controls and dimming

Dimmable	Yes
----------	-----

Mechanical and housing

Cap-base information	4P
----------------------	----


Approval and application

Energy Efficiency Class	G
Mercury (Hg) content (max.)	2 mg
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	25 kWh
	423266

Product data

Full product code	871150070671340
Order product name	MASTER PL-L 24W/830/4P 1CT/25
EAN/UPC – product	8711500706713
Order code	70671340
SAP numerator – quantity per pack	1
Local code description	8344710
Numerator – packs per outer box	25
SAP material	927903208370
Net Weight (Piece)	82.000 g
ILCOS code	FSD-24/30/1B-E-2G11

Dimensional drawing



MASTER PL-L 24W/830/4P 1CT/25

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 24W/830/4P 1CT/25	39.0 mm	18.0 mm	289.2 mm	315 mm	321.6 mm

MASTER PL-L 4 Pin

Photometric data



LDPB_PLL4P_830-Spectral power distribution B/W

Lightcolour /830

