



Actinic BL PL-S/PL-L

PL-L 24W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	2G11 [2G11]	Power (Rated) (Nom)	24 W
Main application	Insect traps	Lamp current (nom.)	0.345 A
Life to 50% failures (nom.)	15000 h	Voltage (Nom)	87 V
Useful life (nom.)	2000 h		
Light Technical		Mechanical and Housing	
Colour Code	210 [leadfree 360 glass (10)]	Cap-base information	4 Pins (4P)
Colour designation	Ultra Violet A	Bulb shape	2xT16
Chromaticity coordinate X (nom.)	228		
Chromaticity coordinate Y (nom.)	230	Approval and Application	
Depreciation at 500 Hours	17 %	Mercury (Hg) content (max.)	4.4 mg
UV Depreciation at 2,000 h	40 %	Mercury (Hg) content (nom.)	4.2 mg
UV depreciation at 5000 hours	60 %		

Actinic BL PL-S/PL-L

UV	
UV-A radiation 100 hours (IEC)	4.9 W
Product Data	
Full product code	871150095206640
Order product name	PL-L 24W/10/4P 1CT/25
EAN/UPC – product	8711500952066

Order code	95206640
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25
SAP material	927903221007
SAP net weight (piece)	82.000 g


Dimensional drawing




PL-L 24W/10/4P 1CT/25

Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 24W/10/4P 1CT/25	18 mm	39 mm	289.2 mm	315 mm	321.6 mm

Photometric data



XDPB_XURPLL_0001-Spectral power distribution B/W



XDPO_XURPLL_0001-Spectral power distribution Colour

