



# MASTER PL-C 2 Pin



## MASTER PL-C 10W/840/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information			
Cap base	G24D-1 [ G24d-1]	Luminous flux (nom.)	600 lm
Life to 10% failures (nom.)	6500 h	Luminous flux (rated) (nom.)	600 lm
Life to 50% failures (nom.)	10000 h	Colour designation	Cool White (CW)
LSF 2000 h Rated	99 %	Chromaticity coordinate X (nom.)	0.38
LSF 4000 h Rated	98 %	Chromaticity coordinate Y (nom.)	0.38
LSF 6000 h Rated	92 %	Correlated Colour Temperature (Nom)	4000 K
LSF 8000 h Rated	78 %	Luminous efficacy (rated) (nom.)	60 lm/W
	Sphere	Colour rendering index (nom.)	80
		LLMF 2000 h Rated	92 %
		LLMF 4000 h Rated	87 %
		LLMF 6000 h Rated	83 %
Light Technical			
Colour Code	841 [ CCT of 4100K (841)]		

# MASTER PL-C 2 Pin

LLMF 8000 h Rated	81 %
<b>Operating and Electrical</b>	
Power (Rated) (Nom)	10.4 W
Lamp current (nom.)	0.190 A
<b>Temperature</b>	
Design temperature (nom.)	28 °C
<b>Controls and Dimming</b>	
Dimmable	No
<b>Mechanical and Housing</b>	
Cap-base information	2P
<b>Approval and Application</b>	
Energy Efficiency Class	G

Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	11 kWh
	423275
<b>Product Data</b>	
Full product code	871150070498670
Order product name	MASTER PL-C 10W/840/2P 1CT/5X10BOX
EAN/UPC – product	8711500704986
Order code	70498670
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	927903884040
SAP net weight (piece)	45.000 g
ILCOS code	FSQ-10/40/1B-I-G24d-1


## Dimensional drawing




MASTER PL-C 10W/840/2P 1CT/5X10BOX

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	117.4 mm

## Photometric data



LDPB\_PLC2P\_840-Spectral power distribution B/W



Lightcolour /840

# MASTER PL-C 2 Pin

## Lifetime



LDLE\_PLC2P\_0001-Life expectancy diagram

LDLE\_PLC2P\_0002-Life expectancy diagram



LDLM\_PLC2P\_0001-Lumen maintenance diagram

