



MASTER PL-C 2 Pin

MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	G24D-1 [G24d-1]	Luminous flux (rated) (nom.)	925 lm
Life to 10% failures (nom.)	6500 h	Colour designation	Warm White (WW)
Life to 50% failures (nom.)	10000 h	Correlated Colour Temperature (Nom)	3000 K
LSF 2000 h Rated	99 %	Luminous efficacy (rated) (nom.)	69 lm/W
LSF 4000 h Rated	98 %	Colour rendering index (nom.)	82
LSF 6000 h Rated	92 %	LLMF 2000 h Rated	92 %
LSF 8000 h Rated	78 %	LLMF 4000 h Rated	87 %
		LLMF 6000 h Rated	83 %
		LLMF 8000 h Rated	81 %
Light Technical			
Colour Code	830 [CCT of 3,000 K]	Power (Rated) (Nom)	13.4 W
Luminous flux (nom.)	925 lm		

MASTER PL-C 2 Pin

Lamp current (nom.)	0.170 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-base information	2P
Approval and Application	
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	17 kWh

Product Data	
Full product code	871150026922500
Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
EAN/UPC – product	8711500269225
Order code	26922500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	927904883001
SAP net weight (piece)	53.600 g
ILCOS code	FSQ-13/30/1B-I-G24d-1


Dimensional drawing




PL-C 13W/830/2P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

Photometric data



LDPB_PLC2P_830-Spectral power distribution B/W



Lightcolour /830

MASTER PL-C 2 Pin

Lifetime



LDLE_PLC2P_0001-Life expectancy diagram

LDLE_PLC2P_0002-Life expectancy diagram



LDLM_PLC2P_0001-Lumen maintenance diagram

