



# MASTER PL-C 4 Pin

## MASTER PL-C 13W/830/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G24Q-1 [ G24q-1]
Life to 50% failures preheat (nom.)	13000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	98 %
LSF preheat 6,000 hours rated	97 %
LSF preheat 8,000 hours rated	90 %
Light Technical	
Colour Code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	900 lm
Luminous flux (rated) (nom.)	900 lm
Colour designation	Warm White (WW)


Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	72 lm/W
Colour rendering index (nom.)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	13.0 W
Lamp current (nom.)	0.170 A

# MASTER PL-C 4 Pin

Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	15 kWh

Product Data	
Full product code	871150062331770
Order product name	MASTER PL-C 13W/830/4P 1CT/5X10BOX
EAN/UPC – product	8711500623317
Order code	62331770
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	927907183040
SAP net weight (piece)	49.900 g
ILCOS code	FSQ-13/30/1B-E-G24q=1



## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

PL-C 13W/830/4P

## Photometric data



LDPB\_PLC4P\_830-Spectral power distribution B/W

Lightcolour /830

# MASTER PL-C 4 Pin

## Lifetime



LDLE\_PLC4P\_0001-Life expectancy diagram

LDLE\_PLC4P\_0002-Life expectancy diagram



LDLM\_PLC4P\_0001-Lumen maintenance diagram

