



# Actinic BL TL(-K)/TL-D(-K)

## Actinic BL TL 40W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		UV depreciation at 5000 hours	
Cap base	G13 [ Medium Bi-Pin Fluorescent]		40 %
Main application	Insect traps	Operating and Electrical	
Life to 50% failures (nom.)	9000 h	Power (Rated) (Nom)	39 W
Useful life (nom.)	5000 h	Lamp current (nom.)	0.43 A
System description	Rapid Start (RS)	Voltage (Nom)	101 V
Light Technical		Mechanical and Housing	
Colour Code	10	Bulb shape	T12 [ 38 mm (T12)]
Colour designation	Actinic	Approval and Application	
Chromaticity coordinate X (nom.)	220	Mercury (Hg) content (nom.)	13.0 mg
Chromaticity coordinate Y (nom.)	205		
UV Depreciation at 2,000 h	20 %		


# Actinic BL TL(-K)/TL-D(-K)

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	10.0 W
UV-A radiation 0 hours (IEC)	12.4 W
Product Data	
Full product code	871150026026000
Order product name	Actinic BL TL 40W/10 SLV/25

EAN/UPC – product	8711500260260
Order code	26026000
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25
SAP material	928011301020
SAP net weight (piece)	292.000 g


## Dimensional drawing

Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37.25 mm	1198.4 mm	1205.4 mm	1212.4 mm




Actinic BL TL 40W/10 SLV/25

## Photometric data



XDPB\_XUVATLRS\_10-Spectral power distribution B/W



XDPO\_XUVATLRS\_10-Spectral power distribution Colour

