



TL-E LIFEMAX

Standard Colours

TL-E 40W/54-765 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

General information	
Cap base	G10Q [G10q]
Life to 50% failures (nom.)	13000 h
Light technical	
Colour Code	54-765
Luminous flux (nom.)	2500 lm
Colour designation	Cool Daylight
Lumen maintenance 10,000 hours (nom.)	73 %
Lumen maintenance 2,000 hours (nom.)	87 %
Lumen maintenance 5,000 hours (nom.)	78 %
Correlated Colour Temperature (Nom)	6200 K
Luminous efficacy (rated) (nom.)	62 lm/W
Colour rendering index (nom.)	72
Operating and electrical	
Power (Rated) (Nom)	40.0 W
Lamp current (nom.)	0.420 A
Voltage (Nom)	110 V
Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb shape	C-T9 [C-T 29 mm (C-T9)]
Approval and application	
Mercury (Hg) content (nom.)	9 mg
Product data	
Full product code	871150055991301
Order product name	TL-E 40W/54-765 1CT/20
EAN/UPC – product	8711500559913
Order code	55991301
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	928027405436
Copy Net Weight (Piece)	0.250 kg
ILCOS code	FSC-40/62/2A-E-G10q-29/400

TL-E LIFEMAX Standard Colours


Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 40W/ 54-765 1CT/20	30.9 mm	27.1 mm	393.7 mm	406.4 mm	341.0 mm	347.7 mm

TL-E 40W/54-765 1CT/20

Photometric data



LDPB_TL-ESTD_54-765-Spectral power distribution B/W



Lightcolour /54-765

