



TL-D Standard Colours

TL-D 36W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap base	G13 [Medium Bi-Pin Fluorescent]	103 V	
Life to 10% failures (nom.)	10000 h	Controls and Dimming	
Life to 50% failures (nom.)	13000 h	Dimmable	Yes
Light Technical		Mechanical and Housing	
Colour Code	33-640	Bulb shape	T8 [26 mm (T8)]
Luminous flux (nom.)	2850 lm	Approval and Application	
Colour designation	Cool White (CW)	Mercury (Hg) content (nom.)	8.0 mg
Lumen maintenance 10,000 hours (nom.)	75 %	Energy consumption kWh/1,000 hours	43 kWh
Lumen maintenance 2,000 hours (nom.)	90 %	Product Data	
Lumen maintenance 5,000 hours (nom.)	80 %	Full product code	871150095045140
Correlated Colour Temperature (Nom)	4100 K	Order product name	TL-D 36W/33-640 1SL/25
Colour rendering index (nom.)	63	EAN/UPC – product	8711500950451
Operating and Electrical		Order code	95045140
Power (Rated) (Nom)	36.0 W	SAP numerator – quantity per pack	1
Lamp current (nom.)	0.440 A		

TL-D Standard Colours

Numerator – packs per outer box	25
SAP material	928048503312
SAP net weight (piece)	135.000 g

ILCOS code	FD-36/41/2B-E-G13
------------	-------------------


Dimensional drawing



TL-D 36W/33-640

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/33-640 15L/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm


Photometric data




LDPB_TL-DSTD_33-640_0001-Spectral power distribution B/W

Lightcolour /33-640

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

