



TL-D Blacklight Blue

TL-D 36W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Main application	Blacklight Blue
Life to 50% failures (nom.)	15000 h
Useful life (nom.)	12000 h
Light Technical	
Colour Code	108 [08 lead-free glass]
Colour designation	Blacklight Blue
LLMF 2000 h Rated	10 %
LLMF 6000 h Rated	15 %
Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.44 A
Voltage (Nom)	103 V
Mechanical and Housing	
Bulb shape	T26 [T 26mm]

Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg
UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	9.5 W
Product Data	
Full product code	871150095115140
Order product name	TL-D 36W BLB 1SL/25
EAN/UPC – product	8711500951151
Order code	95115140
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25
SAP material	928048510805
SAP net weight (piece)	211.000 g


TL-D Blacklight Blue

Dimensional drawing


Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 36W/108

Photometric data



LDPB_TL-DBLB_0001-Spectral power distribution B/W



Lightcolour /108

