



# TL-D Snow White

## TL-D 36W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high colour temperature of the Snow White range creates very cool ambience, making the lamp especially suitable in very hot and dry climate conditions.

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information		Mechanical and housing	
Cap base	G13 [ Medium Bi-Pin Fluorescent]	Bulb shape	T8 [ 26 mm (T8)]
Life to 10% failures (nom.)	10000 h		
Life to 50% failures (nom.)	13000 h		
Light technical		Approval and application	
Luminous flux (nom.)	2370 lm	Mercury (Hg) content (nom.)	5.0 mg
Colour designation	Extreme Cool Daylight	Energy consumption kWh/1,000 hours	43 kWh
Chromaticity coordinate X (nom.)	264	Product data	
Chromaticity coordinate Y (nom.)	280	Full product code	871150089352940
Correlated Colour Temperature (Nom)	12000 K	Order product name	TL-D 36W Snow White 1SL/25
Colour rendering index (nom.)	75	EAN/UPC – product	8711500893529
Operating and electrical		Order code	89352940
Power (Rated) (Nom)	36 W	SAP numerator – quantity per pack	1
Lamp current (nom.)	440 mA	Numerator – packs per outer box	25
Voltage (Nom)	103 V	SAP material	928048545015
		Copy Net Weight (Piece)	135.000 g

## TL-D Snow White

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W Snow White 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 36W Snow White 1SL/25

