



MASTERColour CDM-R

MASTERColour CDM-R 35W/830 E27 PAR30L 30D 1CT

Range of compact, high-efficiency, discharge reflector lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap base	E27 [E27]	Luminous flux (rated) (nom.)	2200 lm
Operating position	UNIVERSAL [Any or Universal (U)]	Luminous intensity (nom.)	7400 cd
Life to 5% failures (nom.)	5000 h	Beam description	Flood [Flood]
Life to 20% failures (nom.)	8000 h	Colour designation	Warm White (WW)
Life to 50% failures (nom.)	8000 h	Chromaticity coordinate X (nom.)	0.431
Switching cycle	1,000X	Chromaticity coordinate Y (nom.)	0.400
		Correlated Colour Temperature (Nom)	3000 K
		Colour rendering index (nom.)	81
		LLMF at end of nominal lifetime (nom.)	48 %
		Luminous flux in 90° cone (rated)	2000 lm
Light Technical		Operating and Electrical	
Colour Code	830 [CCT of 3,000 K]	Power (Rated) (Nom)	39.1 W
Beam Angle (Nom)	30 °	Lamp current (EM) (nom.)	0.53 A
Beam angle technical	29 °		
Beam angle technical	36.3 °		
Beam angle technical	21.8 °		

MASTERCcolour CDM-R

Ignition supply voltage (max.)	198 V
Ignition peak voltage (max.)	5000 V
Ignition supply voltage (min.)	198 V
Re-ignition time (min.) (max.)	15 min
Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	94 V
Voltage (Min)	78 V
Voltage (Nom)	86 V

Controls and Dimming

Dimmable	No
Run-up time 90% (max.)	3 min

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	PAR30L [PAR 3.75 inch/95mm Long]

Approval and Application

Mercury (Hg) content (nom.)	2.8 mg
-----------------------------	--------

Energy consumption kWh/1,000 hours	42 kWh
------------------------------------	--------


Luminaire Design Requirements

Bulb temperature (max.)	300 °C
Cap-base temperature (max.)	200 °C

Product Data

Full product code	871150021170500
Order product name	MASTERCcolour CDM-R 35W/830 E27 PAR30L 30D 1CT
EAN/UPC – product	8711500211705
Order code	21170500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	928071000691
SAP net weight (piece)	0.216 kg
ILCOS code	MRS/UB-35/830-H-E27-95/125/30

Dimensional drawing



MASTERColour CDM-R 35W/830 E27 PAR30L 30D 1CT

Product	D (max)	D	C (max)	C
MASTERColour CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm

Photometric data

171°/190°/130°



MASTERColour CDM-R

Lifetime

