



# MSR

## MSR 1200 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Colour rendering index (nom.)	
Cap base	G22 [ G22]		80
Operating position	UNIVERSAL [ Any or Universal (U)]	Operating and Electrical	
Main application	Studio/Disco	Power (Rated) (Nom)	1200 W
Life to 50% failures (nom.)	800 h	Lamp current (nom.)	13.8 A
System description	Cold Strike	Ignition supply voltage (min.)	207 V
Light Technical		Controls and Dimming	
Colour Code	- [ Not Specified]	Dimmable	No
Luminous flux (min.)	96300 lm	Mechanical and Housing	
Luminous flux (nom.)	107000 lm	Cap-base information	30x53mm
Chromaticity coordinate X (nom.)	325	Luminaire Design Requirements	
Chromaticity coordinate Y (nom.)	327	Bulb temperature (max.)	700 °C
Correlated Colour Temperature (Nom)	5900 K		
Luminous efficacy (rated) (nom.)	89 lm/W		

# MSR

Pinch temperature (max.)	350 °C
<b>Product Data</b>	
Full product code	872790091121300
Order product name	MSR 1200 1CT/3
EAN/UPC – product	8727900911213
Order code	91121300

SAP numerator – quantity per pack	1
Numerator – packs per outer box	3
SAP material	928078105114
SAP net weight (piece)	0.150 kg


## Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200 1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm

MSR 1200 1CT/3

## Photometric data



XDPB\_XDMSR\_CS-Spectral power distribution B/W



XDPO\_XDMSR\_CS-Spectral power distribution Colour

