



MSR Short Arc

MSR 1200 SA 1CT/4

The lamp's short arc and compact design helps enable a compact luminaire that provides high beam intensity, while the excellent color rendition characteristics help ensure optimal colors on stage. The highly innovative P3 technology, developed by Philips, allows MSR Short Arc lamps to be used at higher temperatures in any burning position. The result? Longer lifetime, fewer early failures and a highly consistent performance throughout the lamp's lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GY22 [GY22]
Operating Position	UNIVERSAL [Any or Universal (U)]

Light Technical	
Color Code	- [Not Specified]
Luminous Flux	96,000 lumen
Chromaticity Coordinate X (Nom)	320
Chromaticity Coordinate Y (Nom)	332
Correlated Color Temperature (Nom)	6100 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	65


Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	14 A

Controls and Dimming	
Dimmable	No

Product Data	
Full product code	871829122125800
Order product name	MSR 1200 SA 1CT/4
Order code	22125800
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material number (12NC)	928170905115
Full product name	MSR 1200 SA 1CT/4
EAN/UPC - Case	8718291221265


MSR Short Arc

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR 1200 SA 1CT/4	34 mm	7.0 mm	58 mm	60 mm	59 mm	135 mm

Photometric data



Spectral Power Distribution Colour - MSR 1200 SA 1CT/4

