



# MSR

## MSR 575/2 10H 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Operating and Electrical	
Cap base	GX9.5 [ GX9.5]	Luminous efficacy (rated) (nom.)	83 lm/W
Operating position	UNIVERSAL [ Any or Universal (U)]	Colour rendering index (nom.)	70
Main application	Studio/Disco	Power (Rated) (Nom)	575 W
Life to 50% failures (nom.)	1000 h	Lamp current (nom.)	6.75 A
System description	Cold Strike	Ignition supply voltage (min.)	207 V
Light Technical		Controls and Dimming	
Colour Code	2	Dimmable	No
Luminous flux (min.)	42750 lm	Mechanical and Housing	
Luminous flux (nom.)	47500 lm	Cap-base information	20mm (20)
Chromaticity coordinate X (nom.)	302		
Chromaticity coordinate Y (nom.)	320		
Correlated Colour Temperature (Nom)	6990 K		
Luminous efficacy (rated) (min.)	75 lm/W		

# MSR

## Luminaire Design Requirements


Bulb temperature (max.)	700 °C
Pinch temperature (max.)	350 °C

## Product Data

Full product code	871829122127200
Order product name	MSR 575/2 10H 1CT/4
EAN/UPC – product	8718291221272

Order code	22127200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	928171605115
SAP net weight (piece)	0.057 kg


## Dimensional drawing




MSR 575/2 10H

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575/2	30 mm	7.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
10H 1CT/4		mm			mm			mm	

## Photometric data



XDPB\_XDMSR\_CS-Spectral power distribution B/W



XDPO\_XDMSR\_CS-Spectral power distribution Colour

