



MASTERColour CDM-TC Elite

MASTERColour CDM-TC Elite 35W/942 G8.5 1CT

Compact, single-ended, very high-efficiency, long-life ceramic metal-halide discharge lamp producing crisp white sparkling light with high color rendering

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Lumen maintenance 12,000 hours (nom.) 71 %	
Cap base	G8.5 [G8.5]	Lumen maintenance 10,000 hours (nom.) 73 %	
Operating position	UNIVERSAL [Any or Universal (U)]	Lumen maintenance 2,000 hours (nom.) 84 %	
Life to 5% failures (nom.)	9000 h	Lumen maintenance 5,000 hours (nom.) 79 %	
Life to 10% failures (nom.)	10000 h	Chromaticity coordinate X (nom.)	0.371
Life to 20% failures (nom.)	12000 h	Chromaticity coordinate Y (nom.)	0.366
Life to 50% failures (nom.)	15000 h	Correlated Colour Temperature (Nom)	4200 K
ANSI code HID	-	Luminous efficacy (rated) (nom.)	97 lm/W
		Colour-rendering index (min.)	87
		Colour rendering index (nom.)	90
Light Technical		Operating and Electrical	
Colour Code	942 [CCT of 4,200 K]	Power (Rated) (Nom)	39.1 W
Luminous flux (rated) (min.)	3420 lm	Ignition supply voltage (min.)	198 V
Luminous flux (rated) (nom.)	3800 lm		
Colour designation	Cool White (CW)		

MASTERCLOUR CDM-TC Elite

Re-ignition time (min.) (max.)	15 min
Ignition time (max.)	30 s
Voltage (Max)	97 V
Voltage (Min)	85 V
Voltage (Nom)	91 V

Controls and Dimming

Dimmable	No
Run-up time 90% (max.)	3 min

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	T14 [T 14 mm]

Approval and Application

Mercury (Hg) content (nom.)	4.9 mg
Energy consumption kWh/1,000 hours	43 kWh

UV

PET (NIOSH) (min.)	8 h/500lx
--------------------	-----------

Damage factor D/fc (max.)	0.4
---------------------------	-----

Luminaire Design Requirements

Bulb temperature (max.)	500 °C
Pinch temperature (max.)	300 °C

Product Data

Full product code	871869648469200
Order product name	MASTERCLOUR CDM-TC Elite 35W/942 G8.5 1CT
EAN/UPC – product	8718696484692
Order code	48469200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	928193805129
SAP net weight (piece)	9.000 g
ILCOS code	MT/UB-35/942-H-G8.5-17/85


Dimensional drawing

D

Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERCLOUR CDM-TC Elite 35W/942 G8.5 1CT	15 mm	5.2 mm	51 mm	53 mm	52 mm	85 mm

MASTERCLOUR CDM-TC Elite 35W/942 G8.5 1CT

Photometric data



LDLD_CDMTC-E_0003-Light distribution diagram

MASTERColour CDM-TC Elite

Lifetime

