



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 400 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	PGJX28 [PGJX28]		60
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Light Technical		Power Consumption	400 W
Color Code	- [Not Specified]	Lamp Current (Nom)	7.2 A
Luminous Flux	28,000 lumen	Controls and Dimming	
Chromaticity Coordinate X (Nom)	310	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	320	Product Data	
Correlated Color Temperature (Nom)	6700 K	Full product code	871829115828800
Luminous Efficacy (rated) (Nom)	65 lm/W		

MSR Gold™ MiniFastFit (Touring/Stage)

Order product name	MSR Gold 400 MiniFastFit 1CT/16
Order code	15828800
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material number (12NC)	928194005114

Full product name	MSR Gold™ 400 MiniFastFit 1CT/16
EAN/UPC - Case	8718291158295

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 400 MiniFastFit 1CT/16	23.2 mm	3.0 mm	55 mm	57 mm	56 mm	111 mm	36.5 mm	36 mm	35.3 mm

