



# Classic LEDspotMV

## Essential LED 4.6-50W GU10 827 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

### Product data


General information		Temperature	
Cap base	GU10 [ GU10]	Lamp current (nom.)	39 mA
EU RoHS compliant	Yes	Wattage equivalent	50 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50,000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	4.6-50W	Power factor (nom.)	0.5
Voltage (Nom)		220-240 V	
Light technical		Controls and dimming	
Colour Code	827 [ CCT of 2,700 K]	Dimmable	No
Beam Angle (Nom)	36 °	Mechanical and housing	
Luminous flux (nom.)	395 lm	Bulb shape	PAR16 [ PAR 2 inch]
Luminous intensity (nom.)	700 cd	Approval and application	
Colour designation	Warm White (WW)	Suitable for accent lighting	Yes
Correlated Colour Temperature (Nom)	2700 K	Energy consumption kWh/1,000 hours	5 kWh
Luminous efficacy (rated) (nom.)	85.90 lm/W	Product data	
Colour consistency	<6	Full product code	871869670059400
Colour rendering index (nom.)	80		
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	4.6 W		

# Classic LEDspotMV

Order product name	Essential LED 4.6-50W GU10 827 36D
EAN/UPC – product	8718696700594
Order code	70059400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10

SAP material	929001215208
Copy Net Weight (Piece)	0.038 kg



## Dimensional drawing



Essential LED 4.6-50W GU10 827 36D


Product	D	C
Essential LED 4.6-50W GU10 827 36D	50 mm	54 mm

## Photometric data



LEDspotMV GU10 MR16 827


LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D




LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D

# Classic LEDspotMV

## Lifetime



CLA LEDspotMV 50W GU10 827 36D ND



CLA LEDspotMV 50W GU10 827 36D ND

