



MASTER LEDspot ExpertColor MV

MASTER LED ExpertColor 5.5-50W GU10 930 36D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV and LEDspot Par lamps.

Product data

General Information	
Cap base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	40000 h
Switching cycle	50,000X
Technical type	5.5-50W
Light Technical	
Colour Code	930 [CCT of 3,000 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	405 lm
Luminous intensity (nom.)	800 cd
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	73.64 lm/W
Colour consistency	<3
Colour rendering index (nom.)	97
LLMF at end of nominal lifetime (nom.)	70 %

Luminous flux in 90° cone (rated)	375 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp current (nom.)	30 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Yes

MASTER LEDspot ExpertColor MV

Mechanical and Housing

Bulb shape PARI6 [PAR 2 inch]

Approval and Application

Suitable for accent lighting Yes

Energy consumption kWh/1,000 hours 6 kWh

Product Data

Full product code 871869675590700

Order product name MASTER LED ExpertColor 5.5-50W GU10 930 36D

EAN/UPC – product 8718696755907

Order code 75590700


SAP numerator – quantity per pack 1

Numerator – packs per outer box 10

SAP material 929001347408

SAP net weight (piece) 0.040 kg



Dimensional drawing



GU10 230V5.5W-50W350lm40D 3000K GU10 Dim

Product	D	C
MASTER LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm

Photometric data




MASTER LEDspot ExpertColor MV 50W GU10 930 36D

MASTER LEDspot ExpertColor MV 50W GU10 930 36D

MASTER LEDspot ExpertColor MV

Photometric data



MASTER LEDspot ExpertColor MV 50W GU10 930 36D

Lifetime



MASTER LEDspot ExpertColor MV 35W GU10 25D



MASTER LEDspot ExpertColor MV 35W GU10 25D

