



MASTER LEDspot PAR High Lumen

Master LED PAR30L 32W 30D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data

General information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	32-50W
Light technical	
Colour Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	30 °
Luminous flux (nom.)	3000 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	93.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	32 W
Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and application	
Suitable for accent lighting	Yes

MASTER LEDspot PAR High Lumen

Energy consumption kWh/1,000 hours	32 kWh
Product data	
Full product code	871869673146800
Order product name	Master LED PAR30L 32W 30D 840
EAN/UPC – product	8718696731468
Order code	73146800

SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	929001354808
Copy Net Weight (Piece)	0.410 kg


Dimensional drawing




Master LED PAR30L 32W 30D 840

Product	D	C
Master LED PAR30L 32W 30D 840	95.5 mm	129 mm


Photometric data



LEDspot PAR30L E27 32W 4000K 30D



LEDspot PAR30L E27 32W 4000K 30D



LEDspot PAR30L E27 32W 4000K 30D

MASTER LEDspot PAR High Lumen

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

