



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 32W 30D 857

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	32-50W
Light Technical	
Colour Code	857 [ CCT of 5,700 K]
Beam Angle (Nom)	30 °
Luminous flux (nom.)	3000 lm
Colour designation	Daylight
Correlated Colour Temperature (Nom)	5700 K
Luminous efficacy (rated) (nom.)	93.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	32 W
Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	PAR30L [ PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable for accent lighting	Yes

# MASTER LEDspot PAR High Lumen

Energy consumption kWh/1,000 hours	32 kWh
<b>Product Data</b>	
Full product code	871869673148200
Order product name	Master LED PAR30L 32W 30D 857
EAN/UPC – product	8718696731482
Order code	73148200

SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	929001354908
SAP net weight (piece)	0.410 kg


## Dimensional drawing




PAR30L 220-240V 32-70W 30D 5700K E27 ND

Product	D	C
Master LED PAR30L 32W 30D 857	95.5 mm	129 mm


## Photometric data



LEDspot PAR30L E27 5700K 30D



LEDspot PAR30L E27 5700K 30D



© 2021 Philips Lighting B.V. All rights reserved. Page 10

LEDspot PAR30L E27 5700K 30D

# MASTER LEDspot PAR High Lumen

## Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

