



A 1:1 retrofit replacement for every project where light really matters

CoreLine tempo large

CoreLine tempo large delivers on the CoreLine promise of innovative, easy to use and high quality luminaires. A narrow range of options makes it easy to find the best lux-for-lux replacement for 150W, 250W, and 400W HID lamps. The CoreLine tempo large floodlighting range offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. The installation is made easy thanks to the U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor areas such as tempo floodlights for industrial/commercial areas, parking lots, etc.

Benefits

- The same light levels as your existing conventional solution while saving on energy
- High quality bvp130 tempo large floodlight
- Easy to use
- The option of asset management and/or wireless lighting control

Coreline tempo large


Features

- All standard Ledgine O platform light distributions, lumen packages from 16,000 lm up to 26,000 lm
- Seaside-resistant treatment and swimming pool protection options
- Long lifetime of 75,000 hours, integrated surge protection, the option of an additional surge protection device, high impact resistance IK08, IP66
- Plug and play installation with 1m cable and IP66 connector, horizontal bracket for pole top mounting
- Ready to be connected to Interact City and Interact Sports recreational thanks to an SR socket

Application

- Indoor multi-purpose gymnasiums and swimming pool
- Outdoor recreational sports fields e.g. basket courts, etc.
- Harbors, airports, parking lots

Dimensional drawing



Product details



Coreline_tempo_large-BVP130-DP01.tif




Coreline_tempo_large-BVP130-DP02.tif

Coreline tempo large

Product details



Coreline_tempo_large-BVP130-DP03.tif



Coreline_tempo_large-BVP130-DP04.tif



Coreline_tempo_large-BVP130-DP05.tif



Coreline_tempo_large-BVP130-DP06.tif



Coreline_Tempo_Large-BVP125-DPP.TIF

Coreline tempo large

General Information

CE mark	Yes
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	Yes
Number of gear units	1 unit
Product family code	BVP130

Light Technical

Optical cover/lens type	Flat glass
Color rendering index (CRI)	70
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Gray
---------------	------

Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP66
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

General Information

Order Code	Full Product Name	Lamp family code	Service tag
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	LED260-4S	-
912300023661	BVP130 LED210-4S/740 PSU OFA52 ALU C1KC3	LED210-4S	-
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	LED160-4S	-
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	LED260-4S	-
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	LED210-4S	-
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	LED160-4S	Yes
912300057768	BVP130 LED260-4S/730 A	LED260	-

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	
				Temperature (Nom)	Luminous Flux
912300023660	BVP130	52° x 102°	740	4000 K	26,000 lumen
	LED260-4S/740		neutral		
	PSU OFA52 ALU C1KC3		white		
912300023661	BVP130	52° x 102°	740	4000 K	21,000 lumen
	LED210-4S/740		neutral		
	PSU OFA52 ALU C1KC3		white		
912300023662	BVP130	52° x 102°	740	4000 K	16,000 lumen
	LED160-4S/740		neutral		
	PSU OFA52 ALU C1KC3		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	
				Temperature (Nom)	Luminous Flux
912300023663	BVP130	70° x 21°	740	4000 K	26,000 lumen
	LED260-4S/740		neutral		
	PSU S ALU C1KC3 T35		white		
912300023664	BVP130	70° x 21°	740	4000 K	21,000 lumen
	LED210-4S/740		neutral		
	PSU S ALU C1KC3		white		
912300023665	BVP130	70° x 21°	740	4000 K	16,000 lumen
	LED160-4S/740		neutral		
	PSU S ALU C1KC3		white		

Coreline tempo large

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color	
				Temperature (Nom)	Luminous Flux
912300057768	BVP130 LED260-4S/730 A	52° x 102°	730	3000 K	26,000 lumen
			warm white		

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type outdoor
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	80	Asymmetrical
912300023661	BVP130 LED210-4S/740 PSU OFA52 ALU C1KC3	80	Asymmetrical
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	60	Asymmetrical
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	80	Symmetrical

Order Code	Full Product Name	Number of light sources	Optic type outdoor
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	80	Symmetrical
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	60	Symmetrical
912300057768	BVP130 LED260-4S/730 A	-	Asymmetrical

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	182 W
912300023661	BVP130 LED210-4S/740 PSU OFA52 ALU C1KC3	146 W
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	109 W
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	182 W

Order Code	Full Product Name	Power Consumption
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	146 W
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	109 W
912300057768	BVP130 LED260-4S/730 A	191 W

