



Reliable and flexible

GreenPerform Batten G3 BN398C

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Benefits

- High system efficacy with better energy saving
- Multiple optics for different applications
- Connected for future proof

Features

- System efficiency up to 140lm/W
- Wide and batwing beams available to fit different lighting applications
- DALI and Interact are available for easy control

Application

- Food & large retail
- Warehouse
- Factory
- Indoor public area

Specifications

Mounting type	Suspended Ceiling
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Dimming	PSU PSD POE WIA







Material	Housing: SPCC Cover: PMMA
Main color of the luminaire	WH: RAL 9003
Lumen maintenance at median useful life 50.000h	L70B50
Luminous flux	2000lm~8700lm
Luminaire efficacy	Up to 150lm/W

GreenPerform Batten G3 BN398C

Correlated color temperature - CCT	4000K/6500K
Color Rendering index - CRI	80
Beam angle	WB
Protection Class	Safety class I; Safety class III - POE
IEC61140	





Mechanical impact protection	IK03
Ingress protection	IP20
Overall length	600mm 1200mm 1500mm

Dimensional drawing



GreenPerform Batten G3 BN398C

Dimensional drawing



General Information

CE mark CE mark

Operating and Electrical

Input Voltage 220-240 V

Line Frequency 50 or 60 Hz

Approval and Application

Mech. impact protection code IK03

Ingress protection code IP20

Initial Performance (IEC Compliant)

Initial chromaticity SDCM<5

Luminous flux tolerance +/-10%

General Information

Order Code	Full Product Name	Flammability mark
911401549002	BN398X LED69/840 L1200 L1 S OP	-
911401549102	BN398X LED69/865 L1200 L1 S OP	-
911401549202	BN398X LED70/840 L1500 L1 S OP	-
911401549302	BN398X LED70/865 L1500 L1 S OP	-
911401549402	BN398X LED69/840 L1200 L1 S WB	-
911401549502	BN398X LED69/865 L1200 L1 S WB	-
911401549602	BN398X LED70/840 L1500 L1 S WB	-
911401549702	BN398X LED70/865 L1500 L1 S WB	-
911401549802	BN398X LED20/840 L600 L1 W OP	-

Order Code	Full Product Name	Flammability mark
911401549902	BN398X LED20/865 L600 L1 W OP	-
911401550002	BN398X LED20/840 L600 L1 W WB	-
911401550102	BN398X LED20/865 L600 L1 W WB	-
911401550202	BN398X LED40/840 L1200 L1 W OP	-
911401550302	BN398X LED40/865 L1200 L1 W OP	-
911401550402	BN398X LED40/840 L1200 L1 W WB	-
911401550502	BN398X LED40/865 L1200 L1 W WB	-
911401550602	BN398X LED69/840 L1200 L1 W OP	-
911401550702	BN398X LED69/865 L1200 L1 W OP	-

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Flammability mark	Order Code	Full Product Name	Flammability mark
911401550802	BN398X LED70/840 L1500 L1 W OP	-	911401584651	BN398C LED87/NW L1500 PSD OP	For mounting on normally flammable surfaces
911401550902	BN398X LED70/865 L1500 L1 W OP	-	911401584751	BN398C LED87/CW L1500 PSD OP	For mounting on normally flammable surfaces
911401551002	BN398X LED69/840 L1200 L1 W WB	-	911401584951	BN398C LED20/CW L600 PSU DA	For mounting on normally flammable surfaces
911401551102	BN398X LED69/865 L1200 L1 W WB	-	911401585051	BN398C LED40/NW L1200 PSU DA	For mounting on normally flammable surfaces
911401551202	BN398X LED70/840 L1500 L1 W WB	-	911401585151	BN398C LED40/CW L1200 PSU DA	For mounting on normally flammable surfaces
911401551302	BN398X LED70/865 L1500 L1 W WB	-	911401585251	BN398C LED69/NW L1200 PSU DA	For mounting on normally flammable surfaces
911401564591	BN398X LED20/840 L600 L1 S OP	For mounting on normally flammable surfaces	911401585351	BN398C LED69/CW L1200 PSU DA	For mounting on normally flammable surfaces
911401564691	BN398X LED20/865 L600 L1 S OP	For mounting on normally flammable surfaces	911401585551	BN398C LED87/CW L1500 PSU DA	For mounting on normally flammable surfaces
911401564791	BN398X LED20/840 L600 L1 S WB	For mounting on normally flammable surfaces	911401585651	BN398C LED20/NW L600 PSU WB	For mounting on normally flammable surfaces
911401564891	BN398X LED20/865 L600 L1 S WB	For mounting on normally flammable surfaces	911401585751	BN398C LED20/CW L600 PSU WB	For mounting on normally flammable surfaces
911401564991	BN398X LED40/840 L1200 L1 S OP	For mounting on normally flammable surfaces	911401585851	BN398C LED40/NW L1200 PSU WB	For mounting on normally flammable surfaces
911401565091	BN398X LED40/865 L1200 L1 S OP	For mounting on normally flammable surfaces	911401585951	BN398C LED40/CW L1200 PSU WB	For mounting on normally flammable surfaces
911401565191	BN398X LED40/840 L1200 L1 S WB	For mounting on normally flammable surfaces	911401586051	BN398C LED69/NW L1200 PSU WB	For mounting on normally flammable surfaces
911401565291	BN398X LED40/865 L1200 L1 S WB	For mounting on normally flammable surfaces	911401586151	BN398C LED69/CW L1200 PSU WB	For mounting on normally flammable surfaces
911401583251	BN398C LED20/NW L600 PSU OP	For mounting on normally flammable surfaces	911401586251	BN398C LED87/NW L1500 PSU WB	For mounting on normally flammable surfaces
911401583351	BN398C LED20/CW L600 PSU OP	For mounting on normally flammable surfaces	911401586351	BN398C LED87/CW L1500 PSU WB	For mounting on normally flammable surfaces
911401583451	BN398C LED40/NW L1200 PSU OP	For mounting on normally flammable surfaces	911401587351	BN398C LED40/CW L1200 POE OP	For mounting on normally flammable surfaces
911401583651	BN398C LED69/NW L1200 PSU OP	For mounting on normally flammable surfaces	911401587551	BN398C LED62/CW L1200 POE OP	For mounting on normally flammable surfaces
911401583751	BN398C LED69/CW L1200 PSU OP	For mounting on normally flammable surfaces	911401587851	BN398C LED40/NW L1200 PSU OP TC	For mounting on normally flammable surfaces
911401583851	BN398C LED87/NW L1500 PSU OP	For mounting on normally flammable surfaces	911401587951	BN398C LED40/CW L1200 PSU OP TC	For mounting on normally flammable surfaces
911401584051	BN398C LED20/NW L600 PSD OP	For mounting on normally flammable surfaces			
911401584151	BN398C LED20/CW L600 PSD OP	For mounting on normally flammable surfaces			
911401584251	BN398C LED40/NW L1200 PSD OP	For mounting on normally flammable surfaces			
911401584351	BN398C LED40/CW L1200 PSD OP	For mounting on normally flammable surfaces			

Light Technical

Order Code	Full Product Name	Correlated Color		Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Temperature (Nom)	Optical cover/lens type			
911401549002	BN398X LED69/840 L1200 L1 S OP	4000 K	-	≥80	138 lm/W	6,800 lumen
911401549102	BN398X LED69/865 L1200 L1 S OP	6500 K	-	≥80	138 lm/W	6,800 lumen
911401549202	BN398X LED70/840 L1500 L1 S OP	4000 K	-	≥80	145 lm/W	7,400 lumen
911401549302	BN398X LED70/865 L1500 L1 S OP	6500 K	-	≥80	145 lm/W	7,400 lumen
911401549402	BN398X LED69/840 L1200 L1 S WB	4000 K	-	≥80	127 lm/W	6,900 lumen

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Correlated Color		Color rendering index (CRI)	Luminous Efficacy (rated)	
		Temperature (Nom)	Optical cover/lens type		(Nom)	Luminous Flux
911401549502	BN398X LED69/865 L1200 L1 S WB	6500 K	-	≥80	127 lm/W	6,900 lumen
911401549602	BN398X LED70/840 L1500 L1 S WB	4000 K	-	≥80	135 lm/W	7,100 lumen
911401549702	BN398X LED70/865 L1500 L1 S WB	6500 K	-	≥80	135 lm/W	7,100 lumen
911401549802	BN398X LED20/840 L600 L1 W OP	4000 K	-	>80	145 lm/W	2,200 lumen
911401549902	BN398X LED20/865 L600 L1 W OP	6500 K	-	>80	145 lm/W	2,200 lumen
911401550002	BN398X LED20/840 L600 L1 W WB	4000 K	-	>80	145 lm/W	2,000 lumen
911401550102	BN398X LED20/865 L600 L1 W WB	6500 K	-	>80	145 lm/W	2,000 lumen
911401550202	BN398X LED40/840 L1200 L1 W OP	4000 K	-	>80	140 lm/W	3,700 lumen
911401550302	BN398X LED40/865 L1200 L1 W OP	6500 K	-	>80	140 lm/W	3,700 lumen
911401550402	BN398X LED40/840 L1200 L1 W WB	4000 K	-	>80	145 lm/W	3,800 lumen
911401550502	BN398X LED40/865 L1200 L1 W WB	6500 K	-	>80	145 lm/W	3,800 lumen
911401550602	BN398X LED69/840 L1200 L1 W OP	4000 K	-	>80	138 lm/W	6,800 lumen
911401550702	BN398X LED69/865 L1200 L1 W OP	6500 K	-	>80	138 lm/W	6,800 lumen
911401550802	BN398X LED70/840 L1500 L1 W OP	4000 K	-	>80	145 lm/W	7,400 lumen
911401550902	BN398X LED70/865 L1500 L1 W OP	6500 K	-	>80	145 lm/W	7,400 lumen
911401551002	BN398X LED69/840 L1200 L1 W WB	4000 K	-	>80	127 lm/W	6,900 lumen
911401551102	BN398X LED69/865 L1200 L1 W WB	6500 K	-	>80	127 lm/W	6,900 lumen
911401551202	BN398X LED70/840 L1500 L1 W WB	4000 K	-	>80	135 lm/W	7,100 lumen
911401551302	BN398X LED70/865 L1500 L1 W WB	6500 K	-	>80	135 lm/W	7,100 lumen
911401564591	BN398X LED20/840 L600 L1 S OP	4000 K	Polymethyl methacrylate bowl/cover	>80	146 lm/W	2,200 lumen
911401564691	BN398X LED20/865 L600 L1 S OP	6500 K	Polymethyl methacrylate bowl/cover	>80	146 lm/W	2,200 lumen
911401564791	BN398X LED20/840 L600 L1 S WB	4000 K	Polymethyl methacrylate bowl/cover	>80	148 lm/W	2,000 lumen
911401564891	BN398X LED20/865 L600 L1 S WB	6500 K	Polymethyl methacrylate bowl/cover	>80	148 lm/W	2,000 lumen
911401564991	BN398X LED40/840 L1200 L1 S OP	4000 K	Polymethyl methacrylate bowl/cover	>80	142 lm/W	3,700 lumen
911401565091	BN398X LED40/865 L1200 L1 S OP	6500 K	Polymethyl methacrylate bowl/cover	>80	142 lm/W	3,700 lumen
911401565191	BN398X LED40/840 L1200 L1 S WB	4000 K	Polymethyl methacrylate bowl/cover	>80	146 lm/W	3,800 lumen
911401565291	BN398X LED40/865 L1200 L1 S WB	6500 K	Polymethyl methacrylate bowl/cover	>80	146 lm/W	3,800 lumen
911401583251	BN398C LED20/NW L600 PSU OP	4000 K	Polymethyl methacrylate bowl/cover	>80	147 lm/W	2,100 lumen
911401583351	BN398C LED20/CW L600 PSU OP	6500 K	Polymethyl methacrylate bowl/cover	>80	147 lm/W	2,100 lumen
911401583451	BN398C LED40/NW L1200 PSU OP	4000 K	Polymethyl methacrylate bowl/cover	>80	141 lm/W	4,100 lumen
911401583651	BN398C LED69/NW L1200 PSU OP	4000 K	Polymethyl methacrylate bowl/cover	>80	140 lm/W	6,900 lumen
911401583751	BN398C LED69/CW L1200 PSU OP	6500 K	Polymethyl methacrylate bowl/cover	>80	140 lm/W	6,900 lumen
911401583851	BN398C LED87/NW L1500 PSU OP	4000 K	Polymethyl methacrylate bowl/cover	>80	140 lm/W	8,600 lumen
911401584051	BN398C LED20/NW L600 PSD OP	4000 K	Polymethyl methacrylate bowl/cover	>80	144 lm/W	2,100 lumen
911401584151	BN398C LED20/CW L600 PSD OP	6500 K	Polymethyl methacrylate bowl/cover	>80	144 lm/W	2,100 lumen

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Correlated Color	Optical cover/lens type	Color rendering	Luminous Efficacy (rated)	Luminous Flux
		Temperature (Nom)		index (CRI)	(Nom)	
911401584251	BN398C LED40/NW L1200 PSD OP	4000 K	Polymethyl methacrylate bowl/ cover	>80	136 lm/W	4,100 lumen
911401584351	BN398C LED40/CW L1200 PSD OP	6500 K	Polymethyl methacrylate bowl/ cover	>80	136 lm/W	4,100 lumen
911401584651	BN398C LED87/NW L1500 PSD OP	4000 K	Polymethyl methacrylate bowl/ cover	>80	139 lm/W	8,500 lumen
911401584751	BN398C LED87/CW L1500 PSD OP	6500 K	Polymethyl methacrylate bowl/ cover	>80	139 lm/W	8,500 lumen
911401584951	BN398C LED20/CW L600 PSU DA	6500 K	Polymethyl methacrylate bowl/ cover	>80	129 lm/W	2,000 lumen
911401585051	BN398C LED40/NW L1200 PSU DA	4000 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen
911401585151	BN398C LED40/CW L1200 PSU DA	6500 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen
911401585251	BN398C LED69/NW L1200 PSU DA	4000 K	Polymethyl methacrylate bowl/ cover	>80	123 lm/W	6,800 lumen
911401585351	BN398C LED69/CW L1200 PSU DA	6500 K	Polymethyl methacrylate bowl/ cover	>80	123 lm/W	6,800 lumen
911401585551	BN398C LED87/CW L1500 PSU DA	6500 K	Polymethyl methacrylate bowl/ cover	>80	125 lm/W	8,500 lumen
911401585651	BN398C LED20/NW L600 PSU WB	4000 K	Polymethyl methacrylate bowl/ cover	>80	129 lm/W	2,000 lumen
911401585751	BN398C LED20/CW L600 PSU WB	6500 K	Polymethyl methacrylate bowl/ cover	>80	129 lm/W	2,000 lumen
911401585851	BN398C LED40/NW L1200 PSU WB	4000 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen
911401585951	BN398C LED40/CW L1200 PSU WB	6500 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen
911401586051	BN398C LED69/NW L1200 PSU WB	4000 K	Polymethyl methacrylate bowl/ cover	>80	127 lm/W	7,000 lumen
911401586151	BN398C LED69/CW L1200 PSU WB	6500 K	Polymethyl methacrylate bowl/ cover	>80	127 lm/W	7,000 lumen
911401586251	BN398C LED87/NW L1500 PSU WB	4000 K	Polymethyl methacrylate bowl/ cover	>80	127 lm/W	8,700 lumen
911401586351	BN398C LED87/CW L1500 PSU WB	6500 K	Polymethyl methacrylate bowl/ cover	>80	127 lm/W	8,700 lumen
911401587351	BN398C LED40/CW L1200 POE OP	6500 K	Polymethyl methacrylate bowl/ cover	>80	136 lm/W	4,100 lumen
911401587551	BN398C LED62/CW L1200 POE OP	6500 K	Polymethyl methacrylate bowl/ cover	>80	133 lm/W	6,000 lumen
911401587851	BN398C LED40/NW L1200 PSU OP TC	4000 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen
911401587951	BN398C LED40/CW L1200 PSU OP TC	6500 K	Polymethyl methacrylate bowl/ cover	>80	141 lm/W	4,100 lumen

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401549002	BN398X LED69/840 L1200 L1 S OP	43.65 W	911401549302	BN398X LED70/865 L1500 L1 S OP	45.9 W
911401549102	BN398X LED69/865 L1200 L1 S OP	43.65 W	911401549402	BN398X LED69/840 L1200 L1 S WB	37.8 W
911401549202	BN398X LED70/840 L1500 L1 S OP	45.9 W	911401549502	BN398X LED69/865 L1200 L1 S WB	37.8 W

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Power Consumption
911401549602	BN398X LED70/840 L1500 L1 S WB	46.8 W
911401549702	BN398X LED70/865 L1500 L1 S WB	46.8 W
911401549802	BN398X LED20/840 L600 L1 W OP	13.5 W
911401549902	BN398X LED20/865 L600 L1 W OP	13.5 W
911401550002	BN398X LED20/840 L600 L1 W WB	11.88 W
911401550102	BN398X LED20/865 L600 L1 W WB	11.88 W
911401550202	BN398X LED40/840 L1200 L1 W OP	22.95 W
911401550302	BN398X LED40/865 L1200 L1 W OP	22.95 W
911401550402	BN398X LED40/840 L1200 L1 W WB	24.75 W
911401550502	BN398X LED40/865 L1200 L1 W WB	24.75 W
911401550602	BN398X LED69/840 L1200 L1 W OP	43.65 W
911401550702	BN398X LED69/865 L1200 L1 W OP	43.65 W
911401550802	BN398X LED70/840 L1500 L1 W OP	45.9 W
911401550902	BN398X LED70/865 L1500 L1 W OP	45.9 W
911401551002	BN398X LED69/840 L1200 L1 W WB	37.8 W
911401551102	BN398X LED69/865 L1200 L1 W WB	37.8 W
911401551202	BN398X LED70/840 L1500 L1 W WB	46.8 W
911401551302	BN398X LED70/865 L1500 L1 W WB	46.8 W
911401564591	BN398X LED20/840 L600 L1 S OP	16.5 W
911401564691	BN398X LED20/865 L600 L1 S OP	16.5 W
911401564791	BN398X LED20/840 L600 L1 S WB	14.85 W
911401564891	BN398X LED20/865 L600 L1 S WB	14.85 W
911401564991	BN398X LED40/840 L1200 L1 S OP	28.6 W
911401565091	BN398X LED40/865 L1200 L1 S OP	28.6 W
911401565191	BN398X LED40/840 L1200 L1 S WB	28.6 W
911401565291	BN398X LED40/865 L1200 L1 S WB	28.6 W
911401583251	BN398C LED20/NW L600 PSU OP	14.2 W
911401583351	BN398C LED20/CW L600 PSU OP	14.2 W

Order Code	Full Product Name	Power Consumption
911401583451	BN398C LED40/NW L1200 PSU OP	29 W
911401583651	BN398C LED69/NW L1200 PSU OP	49 W
911401583751	BN398C LED69/CW L1200 PSU OP	49 W
911401583851	BN398C LED87/NW L1500 PSU OP	61 W
911401584051	BN398C LED20/NW L600 PSD OP	14.5 W
911401584151	BN398C LED20/CW L600 PSD OP	14.5 W
911401584251	BN398C LED40/NW L1200 PSD OP	30 W
911401584351	BN398C LED40/CW L1200 PSD OP	30 W
911401584651	BN398C LED87/NW L1500 PSD OP	61 W
911401584751	BN398C LED87/CW L1500 PSD OP	61 W
911401584951	BN398C LED20/CW L600 PSU DA	15.5 W
911401585051	BN398C LED40/NW L1200 PSU DA	29 W
911401585151	BN398C LED40/CW L1200 PSU DA	29 W
911401585251	BN398C LED69/NW L1200 PSU DA	55 W
911401585351	BN398C LED69/CW L1200 PSU DA	55 W
911401585551	BN398C LED87/CW L1500 PSU DA	68 W
911401585651	BN398C LED20/NW L600 PSU WB	15.5 W
911401585751	BN398C LED20/CW L600 PSU WB	15.5 W
911401585851	BN398C LED40/NW L1200 PSU WB	29 W
911401585951	BN398C LED40/CW L1200 PSU WB	29 W
911401586051	BN398C LED69/NW L1200 PSU WB	55 W
911401586151	BN398C LED69/CW L1200 PSU WB	55 W
911401586251	BN398C LED87/NW L1500 PSU WB	68 W
911401586351	BN398C LED87/CW L1500 PSU WB	68 W
911401587351	BN398C LED40/CW L1200 POE OP	30 W
911401587551	BN398C LED62/CW L1200 POE OP	45 W
911401587851	BN398C LED40/NW L1200 PSU OP TC	29 W
911401587951	BN398C LED40/CW L1200 PSU OP TC	29 W

Temperature

Order Code	Full Product Name	Ambient temperature range
911401549002	BN398X LED69/840 L1200 L1 S OP	0 to +30 °C
911401549102	BN398X LED69/865 L1200 L1 S OP	0 to +30 °C
911401549202	BN398X LED70/840 L1500 L1 S OP	0 to +30 °C
911401549302	BN398X LED70/865 L1500 L1 S OP	0 to +30 °C
911401549402	BN398X LED69/840 L1200 L1 S WB	0 to +30 °C
911401549502	BN398X LED69/865 L1200 L1 S WB	0 to +30 °C
911401549602	BN398X LED70/840 L1500 L1 S WB	0 to +30 °C
911401549702	BN398X LED70/865 L1500 L1 S WB	0 to +30 °C
911401549802	BN398X LED20/840 L600 L1 W OP	-20 to +40 °C
911401549902	BN398X LED20/865 L600 L1 W OP	-20 to +40 °C
911401550002	BN398X LED20/840 L600 L1 W WB	-20 to +40 °C
911401550102	BN398X LED20/865 L600 L1 W WB	-20 to +40 °C
911401550202	BN398X LED40/840 L1200 L1 W OP	-20 to +40 °C
911401550302	BN398X LED40/865 L1200 L1 W OP	-20 to +40 °C
911401550402	BN398X LED40/840 L1200 L1 W WB	-20 to +40 °C
911401550502	BN398X LED40/865 L1200 L1 W WB	-20 to +40 °C
911401550602	BN398X LED69/840 L1200 L1 W OP	-20 to +40 °C
911401550702	BN398X LED69/865 L1200 L1 W OP	-20 to +40 °C
911401550802	BN398X LED70/840 L1500 L1 W OP	-20 to +40 °C
911401550902	BN398X LED70/865 L1500 L1 W OP	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401551002	BN398X LED69/840 L1200 L1 W WB	-20 to +40 °C
911401551102	BN398X LED69/865 L1200 L1 W WB	-20 to +40 °C
911401551202	BN398X LED70/840 L1500 L1 W WB	-20 to +40 °C
911401551302	BN398X LED70/865 L1500 L1 W WB	-20 to +40 °C
911401564591	BN398X LED20/840 L600 L1 S OP	0 to +30 °C
911401564691	BN398X LED20/865 L600 L1 S OP	0 to +30 °C
911401564791	BN398X LED20/840 L600 L1 S WB	0 to +30 °C
911401564891	BN398X LED20/865 L600 L1 S WB	0 to +30 °C
911401564991	BN398X LED40/840 L1200 L1 S OP	0 to +30 °C
911401565091	BN398X LED40/865 L1200 L1 S OP	0 to +30 °C
911401565191	BN398X LED40/840 L1200 L1 S WB	0 to +30 °C
911401565291	BN398X LED40/865 L1200 L1 S WB	0 to +30 °C
911401583251	BN398C LED20/NW L600 PSU OP	-20 to +40 °C
911401583351	BN398C LED20/CW L600 PSU OP	-20 to +40 °C
911401583451	BN398C LED40/NW L1200 PSU OP	-20 to +40 °C
911401583651	BN398C LED69/NW L1200 PSU OP	-20 to +40 °C
911401583751	BN398C LED69/CW L1200 PSU OP	-20 to +40 °C
911401583851	BN398C LED87/NW L1500 PSU OP	-20 to +40 °C
911401584051	BN398C LED20/NW L600 PSD OP	-20 to +40 °C
911401584151	BN398C LED20/CW L600 PSD OP	-20 to +40 °C

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Ambient temperature range
911401584251	BN398C LED40/NW L1200 PSD OP	-20 to +40 °C
911401584351	BN398C LED40/CW L1200 PSD OP	-20 to +40 °C
911401584651	BN398C LED87/NW L1500 PSD OP	-20 to +40 °C
911401584751	BN398C LED87/CW L1500 PSD OP	-20 to +40 °C
911401584951	BN398C LED20/CW L600 PSU DA	-20 to +40 °C
911401585051	BN398C LED40/NW L1200 PSU DA	-20 to +40 °C
911401585151	BN398C LED40/CW L1200 PSU DA	-20 to +40 °C
911401585251	BN398C LED69/NW L1200 PSU DA	-20 to +40 °C
911401585351	BN398C LED69/CW L1200 PSU DA	-20 to +40 °C
911401585551	BN398C LED87/CW L1500 PSU DA	-20 to +40 °C
911401585651	BN398C LED20/NW L600 PSU WB	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401585751	BN398C LED20/CW L600 PSU WB	-20 to +40 °C
911401585851	BN398C LED40/NW L1200 PSU WB	-20 to +40 °C
911401585951	BN398C LED40/CW L1200 PSU WB	-20 to +40 °C
911401586051	BN398C LED69/NW L1200 PSU WB	-20 to +40 °C
911401586151	BN398C LED69/CW L1200 PSU WB	-20 to +40 °C
911401586251	BN398C LED87/NW L1500 PSU WB	-20 to +40 °C
911401586351	BN398C LED87/CW L1500 PSU WB	-20 to +40 °C
911401587351	BN398C LED40/CW L1200 POE OP	0 to +40 °C
911401587551	BN398C LED62/CW L1200 POE OP	0 to +40 °C
911401587851	BN398C LED40/NW L1200 PSU OP TC	-20 to +40 °C
911401587951	BN398C LED40/CW L1200 PSU OP TC	-20 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401549002	BN398X LED69/840 L1200 L1 S OP	Only with specific dimmers
911401549102	BN398X LED69/865 L1200 L1 S OP	Only with specific dimmers
911401549202	BN398X LED70/840 L1500 L1 S OP	Only with specific dimmers
911401549302	BN398X LED70/865 L1500 L1 S OP	Only with specific dimmers
911401549402	BN398X LED69/840 L1200 L1 S WB	Only with specific dimmers
911401549502	BN398X LED69/865 L1200 L1 S WB	Only with specific dimmers
911401549602	BN398X LED70/840 L1500 L1 S WB	Only with specific dimmers
911401549702	BN398X LED70/865 L1500 L1 S WB	Only with specific dimmers
911401549802	BN398X LED20/840 L600 L1 W OP	Wireless Dim
911401549902	BN398X LED20/865 L600 L1 W OP	Wireless Dim
911401550002	BN398X LED20/840 L600 L1 W WB	Wireless Dim
911401550102	BN398X LED20/865 L600 L1 W WB	Wireless Dim
911401550202	BN398X LED40/840 L1200 L1 W OP	Wireless Dim
911401550302	BN398X LED40/865 L1200 L1 W OP	Wireless Dim
911401550402	BN398X LED40/840 L1200 L1 W WB	Wireless Dim
911401550502	BN398X LED40/865 L1200 L1 W WB	Wireless Dim
911401550602	BN398X LED69/840 L1200 L1 W OP	Wireless Dim
911401550702	BN398X LED69/865 L1200 L1 W OP	Wireless Dim
911401550802	BN398X LED70/840 L1500 L1 W OP	Wireless Dim
911401550902	BN398X LED70/865 L1500 L1 W OP	Wireless Dim
911401551002	BN398X LED69/840 L1200 L1 W WB	Wireless Dim
911401551102	BN398X LED69/865 L1200 L1 W WB	Wireless Dim
911401551202	BN398X LED70/840 L1500 L1 W WB	Wireless Dim
911401551302	BN398X LED70/865 L1500 L1 W WB	Wireless Dim
911401564591	BN398X LED20/840 L600 L1 S OP	Yes
911401564691	BN398X LED20/865 L600 L1 S OP	Yes
911401564791	BN398X LED20/840 L600 L1 S WB	Yes
911401564891	BN398X LED20/865 L600 L1 S WB	Yes
911401564991	BN398X LED40/840 L1200 L1 S OP	Yes
911401565091	BN398X LED40/865 L1200 L1 S OP	Yes
911401565191	BN398X LED40/840 L1200 L1 S WB	Yes

Order Code	Full Product Name	Dimmable
911401565291	BN398X LED40/865 L1200 L1 S WB	Yes
911401583251	BN398C LED20/NW L600 PSU OP	No
911401583351	BN398C LED20/CW L600 PSU OP	No
911401583451	BN398C LED40/NW L1200 PSU OP	No
911401583651	BN398C LED69/NW L1200 PSU OP	No
911401583751	BN398C LED69/CW L1200 PSU OP	No
911401583851	BN398C LED87/NW L1500 PSU OP	No
911401584051	BN398C LED20/NW L600 PSD OP	Yes
911401584151	BN398C LED20/CW L600 PSD OP	Yes
911401584251	BN398C LED40/NW L1200 PSD OP	Yes
911401584351	BN398C LED40/CW L1200 PSD OP	Yes
911401584651	BN398C LED87/NW L1500 PSD OP	Yes
911401584751	BN398C LED87/CW L1500 PSD OP	Yes
911401584951	BN398C LED20/CW L600 PSU DA	No
911401585051	BN398C LED40/NW L1200 PSU DA	No
911401585151	BN398C LED40/CW L1200 PSU DA	No
911401585251	BN398C LED69/NW L1200 PSU DA	No
911401585351	BN398C LED69/CW L1200 PSU DA	No
911401585551	BN398C LED87/CW L1500 PSU DA	No
911401585651	BN398C LED20/NW L600 PSU WB	No
911401585751	BN398C LED20/CW L600 PSU WB	No
911401585851	BN398C LED40/NW L1200 PSU WB	No
911401585951	BN398C LED40/CW L1200 PSU WB	No
911401586051	BN398C LED69/NW L1200 PSU WB	No
911401586151	BN398C LED69/CW L1200 PSU WB	No
911401586251	BN398C LED87/NW L1500 PSU WB	No
911401586351	BN398C LED87/CW L1500 PSU WB	No
911401587351	BN398C LED40/CW L1200 POE OP	No
911401587551	BN398C LED62/CW L1200 POE OP	No
911401587851	BN398C LED40/NW L1200 PSU OP TC	No
911401587951	BN398C LED40/CW L1200 PSU OP TC	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401549002	BN398X LED69/840 L1200 L1 S OP	White

Order Code	Full Product Name	Housing Color
911401549102	BN398X LED69/865 L1200 L1 S OP	White

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Housing Color
911401549202	BN398X LED70/840 L1500 L1 S OP	White
911401549302	BN398X LED70/865 L1500 L1 S OP	White
911401549402	BN398X LED69/840 L1200 L1 S WB	White
911401549502	BN398X LED69/865 L1200 L1 S WB	White
911401549602	BN398X LED70/840 L1500 L1 S WB	White
911401549702	BN398X LED70/865 L1500 L1 S WB	White
911401549802	BN398X LED20/840 L600 L1 W OP	White
911401549902	BN398X LED20/865 L600 L1 W OP	White
911401550002	BN398X LED20/840 L600 L1 W WB	White
911401550102	BN398X LED20/865 L600 L1 W WB	White
911401550202	BN398X LED40/840 L1200 L1 W OP	White
911401550302	BN398X LED40/865 L1200 L1 W OP	White
911401550402	BN398X LED40/840 L1200 L1 W WB	White
911401550502	BN398X LED40/865 L1200 L1 W WB	White
911401550602	BN398X LED69/840 L1200 L1 W OP	White
911401550702	BN398X LED69/865 L1200 L1 W OP	White
911401550802	BN398X LED70/840 L1500 L1 W OP	White
911401550902	BN398X LED70/865 L1500 L1 W OP	White
911401551002	BN398X LED69/840 L1200 L1 W WB	White
911401551102	BN398X LED69/865 L1200 L1 W WB	White
911401551202	BN398X LED70/840 L1500 L1 W WB	White
911401551302	BN398X LED70/865 L1500 L1 W WB	White
911401564591	BN398X LED20/840 L600 L1 S OP	White
911401564691	BN398X LED20/865 L600 L1 S OP	White
911401564791	BN398X LED20/840 L600 L1 S WB	White
911401564891	BN398X LED20/865 L600 L1 S WB	White
911401564991	BN398X LED40/840 L1200 L1 S OP	White
911401565091	BN398X LED40/865 L1200 L1 S OP	White
911401565191	BN398X LED40/840 L1200 L1 S WB	White
911401565291	BN398X LED40/865 L1200 L1 S WB	White

Order Code	Full Product Name	Housing Color
911401583251	BN398C LED20/NW L600 PSU OP	White RAL 9003
911401583351	BN398C LED20/CW L600 PSU OP	White RAL 9003
911401583451	BN398C LED40/NW L1200 PSU OP	White RAL 9003
911401583651	BN398C LED69/NW L1200 PSU OP	White RAL 9003
911401583751	BN398C LED69/CW L1200 PSU OP	White RAL 9003
911401583851	BN398C LED87/NW L1500 PSU OP	White RAL 9003
911401584051	BN398C LED20/NW L600 PSD OP	White RAL 9003
911401584151	BN398C LED20/CW L600 PSD OP	White RAL 9003
911401584251	BN398C LED40/NW L1200 PSD OP	White RAL 9003
911401584351	BN398C LED40/CW L1200 PSD OP	White RAL 9003
911401584651	BN398C LED87/NW L1500 PSD OP	White RAL 9003
911401584751	BN398C LED87/CW L1500 PSD OP	White RAL 9003
911401584951	BN398C LED20/CW L600 PSU DA	White RAL 9003
911401585051	BN398C LED40/NW L1200 PSU DA	White RAL 9003
911401585151	BN398C LED40/CW L1200 PSU DA	White RAL 9003
911401585251	BN398C LED69/NW L1200 PSU DA	White RAL 9003
911401585351	BN398C LED69/CW L1200 PSU DA	White RAL 9003
911401585551	BN398C LED87/CW L1500 PSU DA	White RAL 9003
911401585651	BN398C LED20/NW L600 PSU WB	White RAL 9003
911401585751	BN398C LED20/CW L600 PSU WB	White RAL 9003
911401585851	BN398C LED40/NW L1200 PSU WB	White RAL 9003
911401585951	BN398C LED40/CW L1200 PSU WB	White RAL 9003
911401586051	BN398C LED69/NW L1200 PSU WB	White RAL 9003
911401586151	BN398C LED69/CW L1200 PSU WB	White RAL 9003
911401586251	BN398C LED87/NW L1500 PSU WB	White RAL 9003
911401586351	BN398C LED87/CW L1500 PSU WB	White RAL 9003
911401587351	BN398C LED40/CW L1200 POE OP	White RAL 9003
911401587551	BN398C LED62/CW L1200 POE OP	White RAL 9003
911401587851	BN398C LED40/NW L1200 PSU OP TC	White RAL 9003
911401587951	BN398C LED40/CW L1200 PSU OP TC	White RAL 9003

Approval and Application

Order Code	Full Product Name	Protection class IEC
911401549002	BN398X LED69/840 L1200 L1 S OP	Safety class I
911401549102	BN398X LED69/865 L1200 L1 S OP	Safety class I
911401549202	BN398X LED70/840 L1500 L1 S OP	Safety class I
911401549302	BN398X LED70/865 L1500 L1 S OP	Safety class I
911401549402	BN398X LED69/840 L1200 L1 S WB	Safety class I
911401549502	BN398X LED69/865 L1200 L1 S WB	Safety class I
911401549602	BN398X LED70/840 L1500 L1 S WB	Safety class I
911401549702	BN398X LED70/865 L1500 L1 S WB	Safety class I
911401549802	BN398X LED20/840 L600 L1 W OP	Safety class I
911401549902	BN398X LED20/865 L600 L1 W OP	Safety class I
911401550002	BN398X LED20/840 L600 L1 W WB	Safety class I
911401550102	BN398X LED20/865 L600 L1 W WB	Safety class I
911401550202	BN398X LED40/840 L1200 L1 W OP	Safety class I
911401550302	BN398X LED40/865 L1200 L1 W OP	Safety class I
911401550402	BN398X LED40/840 L1200 L1 W WB	Safety class I
911401550502	BN398X LED40/865 L1200 L1 W WB	Safety class I
911401550602	BN398X LED69/840 L1200 L1 W OP	Safety class I
911401550702	BN398X LED69/865 L1200 L1 W OP	Safety class I

Order Code	Full Product Name	Protection class IEC
911401550802	BN398X LED70/840 L1500 L1 W OP	Safety class I
911401550902	BN398X LED70/865 L1500 L1 W OP	Safety class I
911401551002	BN398X LED69/840 L1200 L1 W WB	Safety class I
911401551102	BN398X LED69/865 L1200 L1 W WB	Safety class I
911401551202	BN398X LED70/840 L1500 L1 W WB	Safety class I
911401551302	BN398X LED70/865 L1500 L1 W WB	Safety class I
911401564591	BN398X LED20/840 L600 L1 S OP	Safety class I
911401564691	BN398X LED20/865 L600 L1 S OP	Safety class I
911401564791	BN398X LED20/840 L600 L1 S WB	Safety class I
911401564891	BN398X LED20/865 L600 L1 S WB	Safety class I
911401564991	BN398X LED40/840 L1200 L1 S OP	Safety class I
911401565091	BN398X LED40/865 L1200 L1 S OP	Safety class I
911401565191	BN398X LED40/840 L1200 L1 S WB	Safety class I
911401565291	BN398X LED40/865 L1200 L1 S WB	Safety class I
911401583251	BN398C LED20/NW L600 PSU OP	Safety class I
911401583351	BN398C LED20/CW L600 PSU OP	Safety class I
911401583451	BN398C LED40/NW L1200 PSU OP	Safety class I
911401583651	BN398C LED69/NW L1200 PSU OP	Safety class I

GreenPerform Batten G3 BN398C

Order Code	Full Product Name	Protection class IEC
911401583751	BN398C LED69/CW L1200 PSU OP	Safety class I
911401583851	BN398C LED87/NW L1500 PSU OP	Safety class I
911401584051	BN398C LED20/NW L600 PSD OP	Safety class I
911401584151	BN398C LED20/CW L600 PSD OP	Safety class I
911401584251	BN398C LED40/NW L1200 PSD OP	Safety class I
911401584351	BN398C LED40/CW L1200 PSD OP	Safety class I
911401584651	BN398C LED87/NW L1500 PSD OP	Safety class I
911401584751	BN398C LED87/CW L1500 PSD OP	Safety class I
911401584951	BN398C LED20/CW L600 PSU DA	Safety class I
911401585051	BN398C LED40/NW L1200 PSU DA	Safety class I
911401585151	BN398C LED40/CW L1200 PSU DA	Safety class I
911401585251	BN398C LED69/NW L1200 PSU DA	Safety class I
911401585351	BN398C LED69/CW L1200 PSU DA	Safety class I

Order Code	Full Product Name	Protection class IEC
911401585551	BN398C LED87/CW L1500 PSU DA	Safety class I
911401585651	BN398C LED20/NW L600 PSU WB	Safety class I
911401585751	BN398C LED20/CW L600 PSU WB	Safety class I
911401585851	BN398C LED40/NW L1200 PSU WB	Safety class I
911401585951	BN398C LED40/CW L1200 PSU WB	Safety class I
911401586051	BN398C LED69/NW L1200 PSU WB	Safety class I
911401586151	BN398C LED69/CW L1200 PSU WB	Safety class I
911401586251	BN398C LED87/NW L1500 PSU WB	Safety class I
911401586351	BN398C LED87/CW L1500 PSU WB	Safety class I
911401587351	BN398C LED40/CW L1200 POE OP	Safety class III
911401587551	BN398C LED62/CW L1200 POE OP	Safety class III
911401587851	BN398C LED40/NW L1200 PSU OP TC	Safety class I
911401587951	BN398C LED40/CW L1200 PSU OP TC	Safety class I

