



# TownGuide Performer

## BDP102 LED40/830 II DW PCC SI CLO-DDF1 6

BDP102 | TOWNGUIDE PERF CLASSIC CONE - LED40 | LED module 4000 lm - Distribution wide - Polycarbonate bowl/cover clear

The TownGuide Performer family consists of six recognizable, yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic T, T and Tzero. Each luminaire has the option of a clear (PCC), translucent (PCTR) or frosted (PCF) bowl (except Tzero, which is only available with a clear bowl). With an extensive range of lumen packages, neutral white or warm white LED lights sources, and a range of dedicated optics for lower mounting heights, it's easy to select the version that best suits the specific requirements of your project. All this combined with a long life expectancy of 100,000 operating hours. In addition, TownGuide Performer has a variety of control system options that can make this luminaire an integral part of smart energy-reduction programs. This includes LumiStep, DynaDimmer, and LineSwitch stand-alone dim control, and Coded Mains group control, right up to seamless remote connectivity with Interact lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, there's no need to open the luminaire for installation. The Signify Service tag app offers direct access to all relevant data, ensuring maintenance is easy too. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, there are significant energy and maintenance cost savings compared with conventional lighting.

### Product data

General Information			
Lamp family code	LED40 [LED module 4000 lm]	Number of gear units	1 unit
Light source replaceable	Yes	Driver included	Yes
		Photocell	-

## TownGuide Performer

Light source engine type	LED
Service tag	Yes
Product family code	BDP102 [TOWNGUIDE PERF CLASSIC CONE]
Lighting Technology	LED
Value ladder	Performance
Embedded control	Constant light output and DynaDimmer fixed presets version 1
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Upward light output ratio	3
Luminous Flux	3,116 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	80
Number of light sources	4
Light source color	830 warm white
Optical cover/lens type	Polycarbonate bowl/cover clear
Luminaire light beam spread	50° x 70°
Optic type outdoor	Distribution wide

### Operating and Electrical

Line Frequency	50 to 60 Hz
Input Voltage	220-240 V
Initial CLO power consumption	30.5 W
Average CLO power consumption	31.5 W
End CLO power consumption	32.5 W
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	32.5 W
Power Factor (Fraction)	0.94
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

### Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-

Constant light output	Yes
-----------------------	-----

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Mounting device	Post-top for diameter 62 mm
Optical cover/lens shape	Conical
Optical cover/lens finish	Clear
Overall height	317 mm
Overall diameter	570 mm
Effective projected area	0.088 m²

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Initial chromaticity	(0.43, 0.40) SDCM <5
Luminous flux tolerance	+/-7%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	94

### Application Conditions

Maximum dim level	50%
Performance ambient temperature Tq	25 °C

### Product Data

Full product code	871829190620900
Order product name	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6
Order code	910500991021
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910500991021
Full product name	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6

## TownGuide Performer

---

EAN/UPC - Case	8718291906209
EAN/UPC - Product/Case	8718291906209

---

### Dimensional drawing

