



# OccuSwitch

## SES LCM1060 Occ PIR WH

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m<sup>2</sup>. A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m<sup>2</sup>. A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

### Product data

General Information	
CE mark	CE mark
EU RoHS compliant	No
Operating and Electrical	
Input frequency	50 or 60 Hz
Input current (nom.)	NA A
Approval and Application	
CSA mark	NA

UL recognised	No
Application Conditions	
Ambient temperature range	-20 to +55 °C
Product Data	
Full product code	692382865736999
Order product name	SES LCM1060 Occ PIR WH
EAN/UPC – product	6923828657369
Order code	65736999
SAP numerator – quantity per pack	1


# OccuSwitch

---

Numerator – packs per outer box	10
SAP material	911401542702

---

## Dimensional drawing



SES LCM1060 Occ PIR WH

