



MASTER PL-C 2 Pin

MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Flux measurement reference	Sphere		82
Cap-Base	G24D-1 [G24d-1]	Operating and Electrical	
Light Technical		Power Consumption	13.8 W
Color Code	830 [CCT of 3000K]	Lamp Current (Nom)	0.170 A
Luminous Flux	925 lumen	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	No
Chromaticity Coordinate X (Nom)	0.44	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.403	Energy Efficiency Class	G
Correlated Color Temperature (Nom)	3000 K	Mercury (Hg) Content (Max)	1.4 mg
Luminous Efficacy (rated) (Nom)	69 lm/W		

MASTER PL-C 2 Pin

Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423279
Product Data	
Full product code	871150062084270
Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Order code	927904883040


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material number (12NC)	927904883040
Full product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
EAN/UPC - Case	8711500715685

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-C 13W/830/2P 1CT/5X10BOX


MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

