



Ecofit Ledtubes T8



Ecofit LEDtube 1500mm 20W 865 T8 I

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Warm-up time to 60% light (nom.)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
EU RoHS compliant	Yes	Power factor (nom.)	0.5
Nominal lifetime (nom.)	15000 h	Voltage (Nom)	220-240 V
Switching cycle	50,000X		
	Sphere		
Light Technical		Temperature	
Colour Code	865 [CCT of 6,500 K]	T-ambient (max.)	45 °C
Beam Angle (Nom)	240 °	T-ambient (min.)	-20 °C
Luminous flux (nom.)	2000 lm	T storage (max.)	65 °C
Colour designation	Cool Daylight	T storage (min.)	-40 °C
Correlated Colour Temperature (Nom)	6500 K	T-Case maximum (nom.)	60 °C
Luminous efficacy (rated) (nom.)	100.00 lm/W		
Colour consistency	<6	Controls and Dimming	
Colour rendering index (nom.)	80	Dimmable	No
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Mechanical and Housing	
Input frequency	50 to 60 Hz	Bulb material	Glass
Power (Rated) (Nom)	20 W	Product length	1500 mm
Starting time (nom.)	0.5 s	Bulb shape	Tube, double-ended
		Approval and Application	
		Energy Efficiency Class	F
		Energy-saving product	Yes

Ecofit Ledtubes T8

Approval marks	RoHS compliance CE marking KEMA Keur certificate
Energy consumption kWh/1,000 hours	20 kWh
	491856
Product Data	
Full product code	871869969710500
Order product name	Ecofit LEDtube 1500mm 20W 865 T8 I

EAN/UPC – product	8718699697105
Order code	69710500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	929001338222
SAP net weight (piece)	0.310 kg



Dimensional drawing



TLED 5ft 220-240V 20-57W 2000lm 6500K


Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 865 T8 I	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm

Photometric data



LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 20W G13 865 24D ND



LEDtube Ecofit 16W G13 865 24D ND



Ecofit Ledtubes T8

Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

Ecofit Ledtubes T8

