



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 20W 30D 830

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	30 degree(s)
Luminous Flux	1,800 lumen
Luminous Intensity (Nom)	5,400 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	20 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	67 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]

# MASTER LEDspot PAR High Lumen

## Approval and Application


Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	20 kWh
EyeComfort	Yes

## Product Data

Full product code	871869673134500
Order product name	Master LED PAR30L 20W 30D 830
Order code	929001354008



Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001354008
Full product name	Master LED PAR30L 20W 30D 830
EAN/UPC - Case	8718696731352
EAN/UPC - Product/Case	8718696731345

## Dimensional drawing



Product	D	C
Master LED PAR30L 20W 30D 830	95.5 mm	129 mm


## Photometric data



Edison Research Ltd. | Accent Lighting BV | Page 11

Spectral Power Distribution Colour - Master LED PAR30L 20W 30D 830



Accent Lighting Spots - Master LED PAR30L 20W 30D 830



Light Distribution Diagram - Master LED PAR30L 20W 30D 830

# MASTER LEDspot PAR High Lumen

## Lifetime



Life Expectancy Diagram - Master LED PAR30L 20W 30D 830

Lumen Maintenance Diagram - Master LED PAR30L 20W 30D 830

