



MASTER LEDspot LV AR111

MAS LED SpotLV 20-100W 930 AR111 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

Product data

General Information	
Cap base	G53 [G53]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	20-100W
Light Technical	
Colour Code	930 [CCT of 3,000 K]
Beam Angle (Nom)	40 °
Luminous flux (nom.)	1250 lm
Luminous intensity (nom.)	2000 cd
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K


Luminous efficacy (rated) (nom.)	62.00 lm/W
Colour consistency	<4
Colour rendering index (nom.)	91
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	- Hz
Power (Rated) (Nom)	20 W
Lamp current (nom.)	2400 mA
Wattage equivalent	100 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7

MASTER LEDspot LV AR111

Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	AR111
Approval and Application	
Suitable for accent lighting	Yes

Energy consumption kWh/1,000 hours	22 kWh
Product Data	
Full product code	871869969079300
Order product name	MAS LED SpotLV 20-100W 930 AR111 40D
EAN/UPC – product	8718699690793
Order code	69079300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	929002240208
SAP net weight (piece)	0.160 kg


Dimensional drawing




MAS LED SpotLV 20-100W 930 AR111 40D

Product	D	C
MAS LED SpotLV 20-100W 930 AR111 40D	111 mm	62 mm

Photometric data




LEDspots 20W AR111 G53 930 15D



LEDspots 20W AR111 G53 930 40D-LDD

MASTER LEDspot LV AR111


Photometric data




© Philips Lighting B.V. 2022. Philips Lighting B.V. Page 1/1

LEDspots 20W AR111 G53 930 40D-ADL

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

