



Beautiful sparkle, trendy design

MASTERColour CDM-R111

The MASTERColour CDM-R111 combines the trendy look of the 111 mm aluminium reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

Benefits

- Low operating costs
- Easy installation
- Relatively low heat output
- Less glare, comfort for shoppers and staff
- Reduced fading risks

Features

- High lamp efficacy
- Long lamp lifetime compared to incandescent and halogen lamps
- The ceramic discharge tube is optimally and stable positioned in the reflector
- Twist & Lock system
- UV-Block burner capsule
- Anti-glare cap design

Application

- Accent and decorative lighting: display lighting with sparkling, theatrical effects, even in surroundings with very high background ambient light levels like shop windows
- General lighting: in downlighters, a warm and comfortable atmosphere can be created

MASTERColour CDM-R111

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing

D

Product	D (max)	C (max)
MASTERColour CDM-R111 35W/942 GX8.5 24D 1CT	111 mm	95 mm
MASTERColour CDM-R111 35W/942 GX8.5 40D 1CT/6	111 mm	95 mm
MASTERColour CDM-R111 70W/942 GX8.5 40D 1CT/6	111 mm	95 mm

MASTERCcolour CDM-R111

Approval and Application

Energy Efficiency Label (EEL)	B
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Re-Ignition Time (Min) (Max)	15 min
Warm Up Time To 60% Light (Nom)	120 s
General Information	
Cap-Base	GX8.5
Operating Position	UNIVERSAL
Light Technical	
Colour Code	942
Colour Designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4200 K
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	R111

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
21387710	CDM-R111 35W/942 24D.1CT/6	43 kWh	3.0 mg
21389110	MASTERCcolour CDM-R111 35W/942 GX8.5 40D 1CT/6	43 kWh	3.0 mg
21395210	MASTERCcolour CDM-R111 70W/942 GX8.5 40D 1CT/6	80 kWh	6.3 mg

Operating and Electrical

Order Code	Full Product Name	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Rated) (Nom)
21387710	CDM-R111 35W/942 24D.1CT/6	94 V	78 V	86 V	39.1 W
21389110	MASTERCcolour CDM-R111 35W/942 GX8.5 40D 1CT/6	94 V	78 V	86 V	39.1 W

Order Code	Full Product Name	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Rated) (Nom)
21395210	MASTERCcolour CDM-R111 70W/942 GX8.5 40D 1CT/6	114 V	79 V	92 V	73.2 W

General Information (1/2)

Order Code	Full Product Name	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)	Life To 5% Failures (Nom)
21387710	CDM-R111 35W/942 24D.1CT/6	6500 h	7000 h	9000 h	6000 h
21389110	MASTERCcolour CDM-R111 35W/942 GX8.5 40D 1CT/6	6500 h	7000 h	9000 h	6000 h

Order Code	Full Product Name	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)	Life To 5% Failures (Nom)
21395210	MASTERCcolour CDM-R111 70W/942 GX8.5 40D 1CT/6	8500 h	9500 h	11000 h	7500 h

General Information (2/2)

Order Code	Full Product Name	Switching Cycle
21387710	CDM-R111 35W/942 24D.1CT/6	800X
21389110	MASTERCcolour CDM-R111 35W/942 GX8.5 40D 1CT/6	800X

Order Code	Full Product Name	Switching Cycle
21395210	MASTERCcolour CDM-R111 70W/942 GX8.5 40D 1CT/6	1,000X

Light Technical (1/2)


MASTERColour CDM-R111

Order Code	Full Product Name	Beam Angle	Beam Description	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)
		(Nom)			
21387710	CDM-R111 35W/942 24D.1CT/6	24 °	Narrow Flood	0.370	0.365
21389110	MASTERColour CDM-R111 35W/942 GX8.5 40D 1CT/6	40 °	Flood	0.370	0.365

Order Code	Full Product Name	Beam Angle	Beam Description	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)
		(Nom)			
21395210	MASTERColour CDM-R111 70W/942 GX8.5 40D 1CT/6	40 °	Flood	0.381	0.370




Light Technical (2/2)

Order Code	Full Product Name	Colour Rendering Index (Nom)	Llmf At			
			End Of Nominal Lifetime (Nom)	Luminous Flux (Rated) (Nom)	Luminous Intensity (Min)	Luminous Intensity (Nom)
21387710	CDM-R111 35W/942 24D.1CT/6	93	65 %	1350 lm	5700 cd	7500 cd
21389110	MASTERColour CDM-R111 35W/942 GX8.5 40D 1CT/6	93	65 %	1350 lm	3000 cd	4000 cd
21395210	MASTERColour CDM-R111 70W/942 GX8.5 40D 1CT/6	96	60 %	2850 lm	6000 cd	8000 cd



MASTERCoulour CDM-R111



Accent Diagrams



LDAC_CDM-R111_35W_24D-Accent diagram

Beam Diagrams

VBA — 2 x 24° 1/2max — 2 x 11° h E₀ d(m)



LDBE_CDM-R111_35W_24D-Beam diagram

LDBE_CDM-R111_35W_40D-Beam diagram

LDBE_CDM-R111_70W_40D-Beam diagram

