



# Product Description

## Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

### Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

### Features

- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas


# Standard Lustre P45 frosted

## Versions



E27, P45, Frosted

## Dimensional drawing



Product	D	C (max)
Standard 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

