



Long life fluorescent lighting

MASTER TL5 High Output Xtra

This TL5 lamp (tube diameter 16 mm) combines the advantages of a TL5 High Output lamp (TL5 HO lamps are optimized for installations requiring high light output and offer excellent lumen maintenance and color rendering) with a long and reliable lifetime. This results in extra-low maintenance costs and saves on expensive spot replacement. Main applications are places where lamp replacement costs and/or costs of disruption are high.

Benefits

- Longer lifetime and fewer early failures mean lower maintenance costs and facilitate change from spot to group replacement
- Less waste and disposal cost at end-of-life
- Allows system miniaturisation with maximum luminaire design freedom

Features

- Significant reduction of early failures through advanced long life technology
- Extra long lifetime
- Designed for high light output and system miniaturization (40% thinner than TL-D lamps)
- Maximum light output reached at approximately 35 °C in free-burning position if an electronic driver with cut-off feature is used
- Low mercury dose

Application

- Where maintenance costs are high, e.g. high ceilings or other hard-to-reach locations
- Department stores, supermarkets, warehouses, production halls and public areas like car parks and railway stations

MASTER TL5 High Output Xtra


Warnings and Safety

- Philips HF Xtreme gear ensures longest lifetime.
- To achieve lifetimes as published for 100% operation, dimming below 30% should not be applied.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Xtra 49W/840 SLV/20	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

