



# CoreLine Waterproof – the clear choice for LED

## CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Benefits

- Up to 50% energy savings compared with TL-D
- Reliable LED technology – maintenance-free
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

### Features

- Reliable integrated LED technology, ensuring maintenance-free installation and a long lifetime
- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets

### Application

- Parking garages
- Warehouses
- General lighting

# CoreLine Waterproof

## Specifications

<b>Ambient Temperature</b>	-20 to +35 °C
	-20 to +40 °C
	0 to +25 °C
<b>Dimming</b>	No, wireless Dim, yes
<b>Driver</b>	Power supply unit with DALI interface (PSD)
	Power supply unit (PSU)
<b>Initial correlated colour temperature</b>	4000 K, 6500 K

<b>Initial input power</b>	15 W, 16 W, 20.5 W, 21 W, 21.5 W, 22 W, 24.3 W, 24.5 W, 25 W,
	25.5 W, 26 W, 27 W, 28.5 W, 28.6 W, 29 W, 29.5 W, 30 W, 30.5
	W, 31 W, 33 W, 34 W, 35 W, 42.9 W, 43 W, 44 W, 45 W, 49 W, 50
	W, 57.1 W, 60 W, 61 W, 63 W
<b>Initial luminous flux</b>	1800, 1900, 2500, 2700, 3100, 3400, 3700, 4000, 5700, 6000,
	7500, 8000 lm
<b>Material</b>	Bracket:
<b>Material</b>	Housing: polycarbonate

## Versions



Coreline Waterproof G2 LSC - LED  
Module, system flux 2700 lm



## Product details



CoreLine Waterproof WT120C G2  
PCU-7DPP



CoreLine Waterproof WT120C G2  
PCU-3DPP



CoreLine Waterproof WT120C G2  
PCU-10DPP




CoreLine Waterproof WT120C G2  
PCU-9DPP

# CoreLine Waterproof

## Product details



CoreLine Waterproof WT120C G2  
PCU-12DPP



CoreLine Waterproof WT120C G2  
PCU-2DPP



CoreLine Waterproof WT120C G2  
PCU-13DPP



CoreLine Waterproof WT120C G2  
PCU-8DPP



CoreLine Waterproof WT120C G2  
PCU-11DPP

## Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

## Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

## General Information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	D
Glow-wire test	850/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	110

## Initial Performance (IEC Compliant)

Init. Colour rendering index	>80
Luminous flux tolerance	+/-10%

## Mechanical and Housing

Colour	Gray
--------	------

## Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
96244900	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C	Not applicable	Yes
88306800	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C	1%	Not applicable
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Not applicable
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C	Not applicable	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-20 to +35 °C	Not applicable	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	Not applicable
88307500	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C	1%	Not applicable
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C	1%	Not applicable
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Not applicable
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-20 to +35 °C	Not applicable	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C	Not applicable	Not applicable
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C	Not applicable	Not applicable
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C	1%	Not applicable
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	Not applicable
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	0 to +25 °C	Not applicable	Yes
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	0 to +25 °C	10%	Not applicable
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	1%	Not applicable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-20 to +35 °C	Not applicable	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	Not applicable
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	0 to +25 °C	Not applicable	Yes
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	1%	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-20 to +35 °C	Not applicable	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C	Not applicable	Not applicable
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C	Not applicable	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	Not applicable
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	0 to +25 °C	Not applicable	Yes
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	0 to +25 °C	10%	Not applicable
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C	1%	Not applicable
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
40929600	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C	Not applicable	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	Not applicable	Not applicable
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
84048000	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
36933499	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	Not applicable	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	Not applicable
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable

## Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
96244900	WT120C G2 LED19S/840 PSU MDU L600	No	96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	No
88306800	WT120C G2 LED19S/840 PSD L600	Yes	16318100	WT120C G2 LED60S/840 PSU WEC L1500	No
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No	16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
96248700	WT120C G2 LED27S/840 PSU MDU L1200	No	88310500	WT120C G2 LED60S/840 PSD L1500	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	No	85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	No
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	No	96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	No
88307500	WT120C G2 LED27S/840 PSD L1200	Yes	39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	Wireless Dim
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes	88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No	40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	No	96286900	WT120C G2 LED80S/840 PSU MDU L1500	No
16316700	WT120C G2 LED40S/840 PSU WEC L1200	No	40929600	WT120C G2 LED80S/840 PSD L1500	Yes
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No	40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No
88309900	WT120C G2 LED40S/840 PSD L1200	Yes	84045900	WT120C G2 LED19S/840 PSU L600	No
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No	84046600	WT120C G2 LED27S/840 PSU L1200	No
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	No	84048000	WT120C G2 LED40S/840 PSU L1200	No
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	Wireless Dim	84049700	WT120C G2 LED60S/840 PSU L1500	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	40928900	WT120C G2 LED80S/840 PSU L1500	No
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No	36933499	WT120C G2 LED40S/865 PSU L1200	No
96267800	WT120C G2 LED34S/840 PSU MDU L1500	No	36934199	WT120C G2 LED34S/865 PSU L1500	No
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	No	36935899	WT120C G2 LED60S/865 PSU L1500	No
88308200	WT120C G2 LED34S/840 PSD L1500	Yes	34976399	WT120C G2 LED18S/840 PSU PCO L600	No
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	No	34977099	WT120C G2 LED25S/840 PSU PCO L1200	No
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	No	34978799	WT120C G2 LED31S/840 PSU PCO L1500	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes	34979499	WT120C G2 LED37S/840 PSU PCO L1200	No
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No	34980099	WT120C G2 LED57S/840 PSU PCO L1500	No
96275300	WT120C G2 LED60S/840 PSU MDU L1500	No	34981799	WT120C G2 LED75S/840 PSU PCO L1500	No

## General Information (1/2)

Order Code	Full Product Name	Beam			Lamp family code	Order Code	Full Product Name	Beam			Lamp family code
		angle of light source	Optical cover/ lens type	Emergency lighting				angle of light source	Optical cover/ lens type	Emergency lighting	
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	MLO	-	LED27S	96248700	WT120C G2 LED27S/840 PSU MDU L1200	-	MLO	-	LED27S
88306800	WT120C G2 LED19S/840 PSD L600	-	MLO	-	LED19S	96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-	MLO	-	LED27S
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	MLO	-	LED27S	85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	-	MLO	EL3	LED27S

## CoreLine Waterproof

Order Code	Full Product Name	Beam angle of light source	Optical cover/ lens type	Emergency lighting	Lamp family code
88307500	WT120C G2 LED27S/840 PSD L1200	-	MLO	-	LED27S
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	-	MLO	EL3	LED27S
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	MLO	-	LED40S
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	MLO	-	LED40S
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	MLO	-	LED40S
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	MLO	-	LED40S
88309900	WT120C G2 LED40S/840 PSD L1200	-	MLO	-	LED40S
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	-	MLO	EL3	LED40S
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	-	MLO	EL3	LED40S
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	MLO	EL3	LED40S
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	-	MLO	EL3	LED40S
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	MLO	-	LED34S
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	MLO	-	LED34S
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	MLO	-	LED34S
88308200	WT120C G2 LED34S/840 PSD L1500	-	MLO	-	LED34S
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	-	MLO	EL3	LED34S
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	-	MLO	EL3	LED34S
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	-	MLO	EL3	LED34S
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	MLO	-	LED60S
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	MLO	-	LED60S
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	MLO	-	LED60S
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	MLO	-	LED60S
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	MLO	-	LED60S

Order Code	Full Product Name	Beam angle of light source	Optical cover/ lens type	Emergency lighting	Lamp family code
88310500	WT120C G2 LED60S/840 PSD L1500	-	MLO	-	LED60S
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	-	MLO	EL3	LED60S
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	-	MLO	EL3	LED60S
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	MLO	EL3	LED60S
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	-	MLO	EL3	LED60S
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	MLO	-	LED80S
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	MLO	-	LED80S
40929600	WT120C G2 LED80S/840 PSD L1500	-	MLO	-	LED80S
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	-	MLO	EL3	LED80S
84045900	WT120C G2 LED19S/840 PSU L600	-°	MLO	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-°	MLO	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-°	MLO	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-°	MLO	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-°	MLO	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-°	-	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-°	-	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-°	-	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-°	MLO	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-°	MLO	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-°	MLO	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-°	MLO	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-°	MLO	-	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-°	MLO	-	-

### General Information (2/2)

# CoreLine Waterproof

Order Code	Full Product Name	Embedded control	Product Family Code
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	WT130C
88306800	WT120C G2 LED19S/840 PSD L600	-	WT130C
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	WT130C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-	WT130C
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-	WT130C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	-	WT130C
88307500	WT120C G2 LED27S/840 PSD L1200	-	WT130C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	-	WT130C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	WT130C
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	WT130C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	WT130C
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	WT130C
88309900	WT120C G2 LED40S/840 PSD L1200	-	WT130C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	-	WT130C
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	MDU	WT130C
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	WT130C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	-	WT130C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	WT130C
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	WT130C
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	WT130C
88308200	WT120C G2 LED34S/840 PSD L1500	-	WT130C
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	-	WT130C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	MDU	WT130C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	-	WT130C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	WT130C

Order Code	Full Product Name	Embedded control	Product Family Code
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	WT130C
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	WT130C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	WT130C
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	WT130C
88310500	WT120C G2 LED60S/840 PSD L1500	-	WT130C
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	-	WT130C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	MDU	WT130C
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	WT130C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	-	WT130C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	WT130C
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	WT130C
40929600	WT120C G2 LED80S/840 PSD L1500	-	WT130C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	-	WT130C
84045900	WT120C G2 LED19S/840 PSU L600	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	-

## Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96244900	WT120C G2 LED19S/840 PSU MDU L600	(0.38,0.38)SDCM<=3	4000 K	119 lm/W	1900 lm
88306800	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3	4000 K	119 lm/W	1900 lm
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	129 lm/W	2700 lm
96248700	WT120C G2 LED27S/840	(0.38,0.38)SDCM<=3	4000 K	126 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU MDU L1200				
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	125 lm/W	2700 lm
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	104 lm/W	2700 lm
88307500	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3	4000 K	123 lm/W	2700 lm



## CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	100 lm/W	2700 lm
91687200	WT120C G2 LED40S/84 0 PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
96257900	WT120C G2 LED40S/84 0 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
16316700	WT120C G2 LED40S/84 0 PSU WEC L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
16317400	WT120C G2 LED40S/84 0 PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
88309900	WT120C G2 LED40S/84 0 PSD L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
85419700	WT120C G2 LED40S/84 0 PSU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	114 lm/W	4000 lm
96263000	WT120C G2 LED40S/84 0 PSU MDU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	114 lm/W	4000 lm
39980100	WT120C G2 LED40S/84 0 IA1 ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	116 lm/W	4000 lm
88312900	WT120C G2 LED40S/84 0 PSD ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	114 lm/W	4000 lm
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3	4000 K	136 lm/W	3400 lm
96267800	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	3400 lm
96268500	WT120C G2 LED34S/840	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	3400 lm

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU MDU TW3 L1500				
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	3400 lm
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	113 lm/W	3400 lm
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	110 lm/W	3400 lm
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	111 lm/W	3400 lm
91688900	WT120C G2 LED60S/84 0 PSU TW3 L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
96275300	WT120C G2 LED60S/84 0 PSU MDU L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
96276000	WT120C G2 LED60S/84 0 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
16318100	WT120C G2 LED60S/84 0 PSU WEC L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
16319800	WT120C G2 LED60S/84 0 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
88310500	WT120C G2 LED60S/84 0 PSD L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
85421000	WT120C G2 LED60S/84 0 PSU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm
96282100	WT120C G2 LED60S/84 0 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm
39981800	WT120C G2 LED60S/84	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm

## CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	0 IA1 ELB3 L1500				
88314300	WT120C G2 LED60S/84 0 PSD ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	118 lm/W	6000 lm
40930200	WT120C G2 LED80S/84 0 PSU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	131 lm/W	8000 lm
96286900	WT120C G2 LED80S/84 0 PSU MDU L1500	(0.38,0.38)	SDCM<=3 4000 K	131 lm/W	8000 lm
40929600	WT120C G2 LED80S/84 0 PSD L1500	(0.38,0.38)	SDCM<=3 4000 K	131 lm/W	8000 lm
40931900	WT120C G2 LED80S/84 0 PSU L1500 ELB3	(0.38,0.38)	SDCM<=3 4000 K	121 lm/W	8000 lm
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)	SDCM<=3 4000 K	127 lm/W	1900 lm
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)	SDCM<=3 4000 K	135 lm/W	2700 lm
84048000	WT120C G2 LED40S/84 0 PSU L1200	(0.38,0.38)	SDCM<=3 4000 K	143 lm/W	4000 lm
84049700	WT120C G2 LED60S/84 0 PSU L1500	(0.38,0.38)	SDCM<=3 4000 K	143 lm/W	6000 lm
40928900	WT120C G2 LED80S/84 0 PSU L1500	(0.38,0.38)	SDCM<=3 4000 K	140 lm/W	8000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
36933499	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)	SDCM<=3 6500 K	140 lm/W	4000 lm
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)	SDCM<=3 6500 K	139 lm/W	3400 lm
36935899	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)	SDCM<=3 6500 K	140 lm/W	6000 lm
34976399	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)	SDCM<=3 4000 K	120 lm/W	1800 lm
34977099	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)	SDCM<=3 4000 K	125 lm/W	2500 lm
34978799	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	129 lm/W	3100 lm
34979499	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)	SDCM<=3 4000 K	132 lm/W	3700 lm
34980099	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	136 lm/W	5700 lm
34981799	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	132 lm/W	7500 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
96244900	WT120C G2 LED19S/840 PSU MDU L600	16 W
88306800	WT120C G2 LED19S/840 PSD L600	16 W
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	21 W
96248700	WT120C G2 LED27S/840 PSU MDU L1200	21.5 W
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	21.5 W
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	25.5 W
88307500	WT120C G2 LED27S/840 PSD L1200	22 W
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	27 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	30 W
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	30 W

Order Code	Full Product Name	Initial input power
16316700	WT120C G2 LED40S/840 PSU WEC L1200	29 W
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	29 W
88309900	WT120C G2 LED40S/840 PSD L1200	30 W
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	34 W
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	35 W
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	33 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	35 W
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	25 W
96267800	WT120C G2 LED34S/840 PSU MDU L1500	25.5 W
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	25.5 W

## CoreLine Waterproof

Order Code	Full Product Name	Initial input power
88308200	WT120C G2 LED34S/840 PSD L1500	26 W
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	29.5 W
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	30.5 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	44 W
96275300	WT120C G2 LED60S/840 PSU MDU L1500	45 W
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	45 W
16318100	WT120C G2 LED60S/840 PSU WEC L1500	44 W
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	44 W
88310500	WT120C G2 LED60S/840 PSD L1500	45 W
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	49 W
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	50 W
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	50 W
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	49 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	60 W
96286900	WT120C G2 LED80S/840 PSU MDU L1500	61 W

Order Code	Full Product Name	Initial input power
40929600	WT120C G2 LED80S/840 PSD L1500	61 W
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	63 W
84045900	WT120C G2 LED19S/840 PSU L600	15 W
84046600	WT120C G2 LED27S/840 PSU L1200	20.5 W
84048000	WT120C G2 LED40S/840 PSU L1200	28.6 W
84049700	WT120C G2 LED60S/840 PSU L1500	42.9 W
40928900	WT120C G2 LED80S/840 PSU L1500	57.1 W
36933499	WT120C G2 LED40S/865 PSU L1200	28.5 W
36934199	WT120C G2 LED34S/865 PSU L1500	24.5 W
36935899	WT120C G2 LED60S/865 PSU L1500	43 W
34976399	WT120C G2 LED18S/840 PSU PCO L600	15 W
34977099	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W
34978799	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W
34979499	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W
34980099	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W
34981799	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W

