



MSD Gold™ MiniFastFit – replacement in seconds + longer life

MSD Gold™ MiniFastFit

The specially designed lamp base of the MSD Gold™ MiniFastFit means that this lamp can be replaced in just seconds, helping to ensure non-stop entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. The lamp's compact size allows for easy handling and compact fixture designs, while the very short arc provides a high perceived brightness and high beam intensity. What's more, the MSD Gold™ MiniFastFit has an extended lifetime, which further reduces lamp replacement costs.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity
- Less lamp replacement

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- Color temperature >8000K
- Very short arc
- Long lifetime (2000hrs)

MSD Gold™ MiniFastFit

Application

- Discos
- Clubs
- Display lighting


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) |
|--------------------|---------|--------|---------|---------|---------|---------|
| MSD Gold™ 300/2 | 23 mm | 5.0 mm | 65.8 mm | 67.8 mm | 66.8 mm | 126 mm |
| MiniFastFit 1CT/16 | | | | | | |

