

# Value-for-money electromagnetic ballast for fluorescent applications

## BT-ALU EM ballasts for TL Fluorescent lamps

Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps; ideal solution for economical high-quality performance

### Benefits

- Reliable electrical and mechanical performance
- Guaranteed quality level, light output >80%
- Noise reduction, thanks to embossed mounting plate

### Features

- Long lifetime
- Quick and easy wiring
- Easy to recognize: blue product label
- Tw marking 130 °C (means average lifetime of 10 years' continuous operation @ 130 °C)
- High-quality screw-in or insert contact

### Application


- Signage
- Parking areas/outdoor
- Industry (low bay)

# BT-ALU EM ballasts for TL Fluorescent lamps

## Versions



## Dimensional drawing



### Product

BT-ALU 18W 220V C SC

