



StoreFlux – powerful LED accent lighting that blends perfectly in the store architecture

StoreFlux gen3 rim

The StoreFlux gridlight can be equipped with up to four LED modules with a special reflector system to deliver top-quality light that makes your shop and merchandise look great. The combination of multiple LED sources with high lumen packages in one luminaire creates sparkling light effects. StoreFlux offers low maintenance compared with CDM and high efficiency compared to halogen.

Benefits

- High-quality accent lighting thanks to PerfectAccent reflector's light signature
- Short payback compared with CDM luminaires due to high system efficacy
- Efficient and low-maintenance thanks to LED technology

Features

- Multiple accent light sources in one luminaire (1, 2, 3 or 4 LED modules)
- High lumen packages: up to 3900 lm per module (up to 3 head version)
- Rim version; rimless variant available; different RAL color combinations possible
- Ease of installation and maintenance (separate installation frame; replaceable LED light engines and reflectors)

Application

- Retail; fashion
- Hospitality

StoreFlux gen3 rim


Specifications

Type	GD601B (rim, 1 head version)	Median useful life L80B50	50,000 hours
	GD602B (rim, 2 head version)		
	GD603B (rim, 3 head version)		
	GD604B (rim, 4 head in a row version)		
	GD605B (rim, 4 head in a square version)		
Light source	Non-replaceable LED module	Median useful life L90B50	25,000 hours
Power (per head)	LED11S: 16.5 W		Driver failure rate
	LED12S: 12.5 W	Average ambient temperature	
	LED20S: 20 W		Operating temperature range
	LED17S: 16 W	Driver	
	LED27S: 25 W		Mains voltage
	LED39S: 39 W	Dimming	
Beam angle	LED12S/17S/27S/39S: 29 and 35°, LED11S/20S: 10°		Material
Luminous flux (at 3000 K)	LED11S: 1100 lm LED12S: 1200 lm LED20S: 2000 lm LED17S: 1700 lm LED27S: 2700 lm LED39S: 3900 lm	Color	
Correlated Color Temperature	2700, 3000 or 4000 K and CrispWhite		Optical cover
Color Rendering Index	80 90 (light color 930) >95 (CRW)	Connection	
Median useful life L70B50	70,000 hours		Cable options
		Maintenance	
			Installation
		Remarks:	


Versions



Tief-/breitstrahlend



Tief-/breitstrahlend



StoreFlux gen3 rim

Product details


Bottom view excluding drivers



Top view excluding drivers



Side view of rotation system



StoreFlux gen3 rim

Application Conditions

Ambient temperature range	+10 to +40 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Optical cover/lens type	ACT
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	F
Glow-wire test	650/5
Light source replaceable	No
Optic type	MB

Initial Performance (IEC Compliant)

Initial chromaticity	(0.43, 0.40) SDCM <3
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	≥80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	White and white
--------	-----------------

General Information

Order Code	Full Product Name	Lamp family code	Number of gear units	Number of light sources	Product Family Code
88118700	GD602B LED27S/830 PSU-E MB WH-WH	LED27S	2 units	2	GD602B
88119400	GD602B LED39S/830 PSU-E MB WH-WH	LED39S	2 units	2	GD602B
88422500	GD602B LED12S/830 PSU-E MB WH-WH	LED12S	2 units	2	GD602B
88420100	GD601B LED12S/830 PSU-E MB WH-WH	LED12S	1 unit	1	GD601B
88425600	GD603B LED17S/830 PSU-E MB WH-WH	LED17S	3 unit	3	GD603B


Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
88118700	GD602B LED27S/830 PSU-E MB WH-WH	120 lm/W	5400 lm	23.5 W
88119400	GD602B LED39S/830 PSU-E MB WH-WH	123.80952380952381 lm/W	7800 lm	32 W
88422500	GD602B LED12S/830 PSU-E MB WH-WH	120 lm/W	2400 lm	10.2 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
88420100	GD601B LED12S/830 PSU-E MB WH-WH	120 lm/W	1200 lm	10 W
88425600	GD603B LED17S/830 PSU-E MB WH-WH	118.05555555555556 lm/W	5100 lm	13.8 W

StoreFlux gen3 rim

Polar Wide Diagrams



IFPS_GD601B 1xLED12S/827 MB-Polar Normal
(separate)

