



# Time to upgrade your conventional lighting to LumiStreet gen2

## LumiStreet gen2

Increasing numbers of municipalities are having to upgrade large-scale conventional street lighting installations with energy-efficient LED technology. But they are having to do this with smaller and smaller budgets. That's why the new generation of LumiStreet has been upgraded and designed to provide a solution to this challenge, it is the ideal solution for performing point-to-point replacement of conventional lighting. LumiStreet gen2 achieves this by offering high-efficiency, low Total Cost of Ownership and ease of installation and maintenance. The ease of installation and maintenance is enabled by the Philips Service tag. Moreover, the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City.

### Benefits

- An economical LED alternative to conventional street lights
- Offers high efficiency and energy savings
- Made of high-quality materials for a longer lifetime and minimised maintenance

### Features

- Good application coverage thanks to wide range of optics, tunable flux and tiltable spigot
- Easy luminaire identification due to the Philips Service tag
- Future-ready thanks to the SR (System Ready) socket
- High system efficiency with good application coverage
- The luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution

# LumiStreet gen2

## Application

- Roads and streets
- Residential streets

## Specifications

Ambient Temperature	-40 to +50 °C
Input voltage	220 to 240 V
Inrush current (A)	53 A
Light source	Yes
replaceable	

Material	Housing: aluminum die-cast
Optic	Distribution medium 11
Type	BGP293

## Versions



## Product details



Bottom view for spigot regulation and screw

UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2

UniStreet\_LumiStreet\_gen2



# LumiStreet gen2

## Product details

### UniStreet gen2 spigot regulation

